




**SOCKETS 10 (3/8")**



3/8"


30

**SOCKET 3/8" hexagon UD profile**

- ▲ Acc. to DIN 3124, ISO 2725-1
- ▲ Square drive as per DIN 3120 - C 10, ISO 1174, with ball retention groove
- ▲ Hand-operated, knurled grip
- ▲ GEDORE vanadium steel 31CrV3, polished, chrome-plated
- ▲ \* not standardised

10

3/8"



mm

Code	No.	*	mm	L	d <sub>1</sub>	d <sub>2</sub>	t	↕	⊞	£
6230160	30 6	*	6	28	9.7	17.5	5.0	24	10	
6230240	30 7		7	28	11.0	17.5	5.0	24	10	
6230320	30 8		8	28	12.1	17.5	9.0	28	10	
6230400	30 9		9	28	13.5	17.5	9.0	27	10	
6230590	30 10		10	28	14.7	17.5	9.0	28	10	
6233850	30 11		11	28	16.0	17.5	9.0	30	10	
6233930	30 12		12	28	17.2	18.3	9.0	33	10	
6234070	30 13		13	28	18.5	17.5	9.0	32	10	
6234150	30 14		14	29	19.7	18.4	11.0	38	10	
6234230	30 15		15	30	21.0	19.7	12.5	44	10	
6234310	30 16		16	30	22.2	21.0	12.5	49	10	
6234580	30 17		17	30	23.5	22.3	12.5	57	10	
6234660	30 18		18	30	24.7	23.0	12.5	62	10	
6234740	30 19		19	30	26.0	23.7	12.5	68	10	
6234820	30 20		20	31	27.2	24.5	12.5	78	5	
6234900	30 21		21	31	28.5	25.8	13.5	86	5	
6235040	30 22		22	32	29.7	26.3	14.5	92	5	
2194783	30 24	*	24	33	32.0	28.0	15.5	120	5	

AF

Code	No.	AF	L	d <sub>1</sub>	d <sub>2</sub>	t	↕	⊞	£
6232100	30 1/4AF	1/4	28	10.1	17.5	5.0	23	10	
6232290	30 9/32AF	9/32	28	11.1	17.5	5.0	24	10	
6232370	30 5/16AF	5/16	28	12.1	17.5	9.0	25	10	
6232450	30 11/32AF	11/32	28	13.1	17.5	9.0	25	10	
6232530	30 3/8AF	3/8	28	14.1	17.5	9.0	26	10	
2101025	30 7/16AF	7/16	28	16.1	17.5	9.0	28	1	
2101033	30 1/2AF	1/2	28	18.1	19.2	9.0	35	1	
2101041	30 9/16AF	9/16	29	20.1	18.7	11.0	39	1	
2101068	30 19/32AF	19/32	30	21.0	19.7	12.5	44	1	
2101076	30 5/8AF	5/8	30	22.1	20.7	12.5	48	1	
2101084	30 11/16AF	11/16	30	24.0	22.7	12.5	60	1	
2101092	30 3/4AF	3/4	30	26.0	23.7	12.5	65	1	
2101106	30 7/8AF	7/8	32	30.0	26.5	14.5	120	1	


D 30

**SOCKET 3/8" bi-hexagon UD profile**

- ▲ Acc. to DIN 3124, ISO 2725-1
- ▲ Square drive as per DIN 3120 - C 10, ISO 1174, with ball retention groove
- ▲ Hand-operated, knurled grip
- ▲ GEDORE vanadium steel 31CrV3, polished, chrome-plated
- ▲ \* not standardised

10

3/8"



mm

Code	No.	*	mm	L	d <sub>1</sub>	d <sub>2</sub>	t	↕	⊞	£
1845705	D 30 6	*	6	28	9.7	17.5	5.0	111	10	
1845713	D 30 7		7	28	11.0	17.5	5.0	24	10	
1845721	D 30 8		8	28	12.1	17.5	9.0	26	10	
1845748	D 30 9		9	28	13.5	17.5	9.0	27	10	
6229230	D 30 10		10	28	14.7	17.5	9.0	28	10	
6230670	D 30 11		11	28	16.0	17.5	9.0	30	5	
6230750	D 30 12		12	28	17.2	18.3	9.0	32	5	
6230830	D 30 13		13	28	18.5	17.5	9.0	31	10	
6230910	D 30 14		14	29	19.7	18.4	11.0	37	5	
6231050	D 30 15		15	30	21.0	19.7	12.5	40	5	
6231130	D 30 16		16	30	22.2	21.0	12.5	49	5	
6231210	D 30 17		17	30	23.5	22.3	12.5	54	10	
6231480	D 30 18		18	30	24.7	23.0	12.5	62	5	
6231560	D 30 19		19	30	26.0	23.7	12.5	64	10	
6231640	D 30 20		20	31	27.2	24.5	12.5	74	5	
6231720	D 30 21		21	31	28.5	25.8	13.5	83	5	
6231800	D 30 22		22	32	29.7	26.3	14.5	87	5	
2194864	D 30 24	*	24	33	32.0	28.0	15.5	100	5	

AF

Code	No.	AF	L	d <sub>1</sub>	d <sub>2</sub>	t	↕	⊞	£
2016613	D 30 1/4AF	1/4	28	10.1	17.5	5.0	50	1	
2101009	D 30 9/32AF	9/32	28	11.1	17.5	5.0	20	1	
2101017	D 30 11/32AF	11/32	28	13.1	17.5	9.0	26	1	
1997130	D 30 3/8AF	3/8	28	14.1	17.5	9.0	10	1	
1997149	D 30 13/32AF	13/32	28	15.0	17.5	9.0	30	1	
6232610	D 30 7/16AF	7/16	28	16.1	17.5	9.0	27	10	
6232880	D 30 1/2AF	1/2	28	18.1	19.2	9.0	34	10	
6232960	D 30 9/16AF	9/16	29	20.1	18.7	11.0	36	10	
6233180	D 30 19/32AF	19/32	30	21.0	19.7	12.5	39	10	
6233260	D 30 5/8AF	5/8	30	22.1	20.7	12.5	44	10	
6233340	D 30 11/16AF	11/16	30	24.0	22.7	12.5	53	10	
6233420	D 30 3/4AF	3/4	30	26.0	23.7	12.5	61	10	
1997157	D 30 25/32AF	25/32	31	27.0	24.3	12.5	75	1	
1997165	D 30 13/16AF	13/16	31	28.0	25.3	12.5	80	1	
6232020	D 30 7/8AF	7/8	32	30.0	26.5	14.5	82	10	
1997173	D 30 15/16AF	15/16	33	31.9	28.0	15.5	110	1	
1983296	D 30 1AF	1	33	33.9	30.0	15.5	120	1	

[www.gedore.com](http://www.gedore.com)