
## compact cylinder ADNGF-25-20-P-A Part number: 554232

According to ISO 21287, with plain-bearing guide, piston rod secured against rotation by means of guide rods and yoke plate.



## **Data sheet**

Feature	Value
Stroke	20 mm
Piston diameter	25 mm
Based on the standard	ISO 21287
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston
	Piston rod
	Profile barrel
Position detection	For proximity sensor
Protection against torque/guide	Guide rod with yoke
Operating pressure	1 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further
	operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-20 80 °C
Impact energy in end positions	0.3 J
Theoretical force at 6 bar, return stroke	247 N
Theoretical force at 6 bar, advance stroke	295 N
Moving mass with 0 mm stroke	85 g
Additional weight per 10 mm stroke	28 g
Basic weight for 0 mm stroke	191 g
Additional mass factor per 10 mm of stroke	11 g
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material cover	Aluminium
	Anodised
Material seals	TPE-U(PUR)
Material piston rod	High alloy steel
Material cylinder barrel	Wrought Aluminium alloy
	Smooth anodised

**FESTO**