

Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Contactor
Control type	Push-button start green I Push-button stop/reset red O





Complementary

Motor power kW	30 kW at 380/400 V AC 50/60 Hz 37 kW at 415 V AC 50/60 Hz 37 kW at 440 V AC 50/60 Hz 37 kW at 500 V AC 50/60 Hz 37 kW at 660/690 V AC 50/60 Hz 18.5 kW at 220/230 V AC 50/60 Hz
[Ith] Conventional free air thermal current	65 A
[Uc] control circuit voltage	380 V AC 50/60 Hz
Cable entry number	1 ISO32 top 3 1 ISO20 + 2 ISO32 bottom
Width	200 mm
Height	300 mm
Depth	158.4 mm
Net weight	4.85 kg

Environment

Material	Sheet steel
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Product certifications	UKCA

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins