


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		F1	REVISED PER ECO-11-005027	11MAR11	RK	HMR





- 1

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 2

WIRE RANGE: 0.2-1mm² [24-18 AWG].
INSULATION RANGE: 1.02-2.54 [.040-.100] DIA.
- 3

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.



GOLD 4	0.30 [.012]	BRASS	1-770252-0
GOLD 1	0.30 [.012]	BRASS	770252-2
PRE-TIN	0.30 [.012]	BRASS	770252-1
FINISH	MATERIAL		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 30SEP04	TE Connectivity			
		CHK C.JONES 30SEP04				
DIMENSIONS: mm [INCHES]		APVD C.JONES 30SEP04	NAME			
		PRODUCT SPEC	PIN, LOOSE PIECE, UNIVERSAL MATE-N-LOK(TM) II			
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-	A2	00779	C=770252	-
CUSTOMER DRAWING			SCALE	SHEET	REV	
			4:1	1 OF 1	F1	

