

STD21W-BLANK

✓ ACTIVE

Agastat 7000

TE Internal #: 1768047-9

Snap-On Pre-Printed Marker, STD 21 Size, White, Chevron Cut, 6.7 mm [.264 in] Width, Black Print, Polyoxymethylene, Agastat 7000

[View on TE.com >](#)



Identification & Labeling > Pre-Printed Markers > STD Snap-On Markers



Marker Style: **Snap-On**

Marker Size: **STD 21**

Compatible Cable Diameter Range: **11 – 15.5 mm [ .433 – .61 in ]**

Primary Product Color: **White**

Marker Cut: **Chevron**

[All STD Snap-On Markers \(957\)](#)

Features

Body Features

|                          |                  |
|--------------------------|------------------|
| Marker Style             | Snap-On          |
| Marker Size              | STD 21           |
| Primary Product Color    | White            |
| Primary Product Material | Polyoxymethylene |

Dimensions

|                                 |                             |
|---------------------------------|-----------------------------|
| Compatible Cable Diameter Range | 11 – 15.5 mm[.433 – .61 in] |
| Product Width                   | 6.7 mm[.264 in]             |

Printer/Label Features

|            |         |
|------------|---------|
| Marker Cut | Chevron |
|------------|---------|

Packaging Features

|                    |     |
|--------------------|-----|
| Packaging Method   | Box |
| Packaging Quantity | 50  |

Other

|                       |       |
|-----------------------|-------|
| Printed Marking Color | Black |
|-----------------------|-------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

STD21W-BLANK

Snap-On Pre-Printed Marker, STD 21 Size, White, Chevron Cut, 6.7 mm [.264 in] Width, Black Print, Polyoxymethylene, Agastat 7000



|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [Agastat 7000](#)

STD21W-BLANK

Snap-On Pre-Printed Marker, STD 21 Size, White, Chevron Cut, 6.7 mm [.264 in] Width, Black Print, Polyoxymethylene, Agastat 7000



AC Relays(8)

DC Relays(33)

Electromechanical Relays(41)

Customers Also Bought

TE Part #CAT-D48-ST273  
DEUTSCH Solid Contacts

TE Part #DT04-2P  
REC, 2P, GRY, N

TE Part #DT06-2S  
PLG, 2P, GRY, N

TE Part #CAT-D487-W416  
Wedgelocks: DEUTSCH DT

TE Part #114017-ZZ  
SEALING PLUG, SIZE 12/16, WHT

TE Part #CAT-AM71-CH8172  
AMP SUPERSEAL 1.5MM,  
CONNECTOR HOUSING

TE Part #281934-2  
SINGLE WIRE SEAL

Documents

Product Drawings

STD21W-BLANK

English

Datasheets & Catalog Pages

STD/STB-type Snap-on Pre-printed Wire & Cable Markers

English

STD and STB Technical Datasheet

English

Product Specifications

RW-2538 STD and STB work instruction

English