



 PRODUCT-DETAILS

OS400D40N2P

OS400D40N2P SWITCH FUSE



General Information

Extended Product Type	OS400D40N2P
Product ID	1SCA022753R3550
EAN	6417019244983
Catalog Description	OS400D40N2P SWITCH FUSE
Long Description	Switch Fuses,Front Operated,4-pole,40 (Right Side),DIN,0,1,2,Handle and shaft included,Switched - With Solid Link

ABB EcoSolutions

ABB Site Meeting Group Waste To Landfill Target	UL 2799 Zero Waste To Landfill Validation available
End Of Life Disassembling Instructions	1SCC311050M0201
Environmental Product Declaration - EPD	1SCC311198D0201

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

Data Sheet, Technical Information	1SCC311013C0201
Instructions and Manuals	1SCC311015M0215
Mechanical Drawings	OS400D40F
Environmental Product Declaration - EPD	1SCC311198D0201

Environmental

Degree of Protection	acc. to IEC 60529 IP20
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

Dimensions

Product Net Width	319 mm
Product Net Height	230 mm
Product Net Depth / Length	193 mm
Product Net Weight	8.41 kg 18.54 lb

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	240 mm 9.45 in
Package Level 1 Depth / Length	335 mm 13.19 in
Package Level 1 Height	206 mm 8.11 in
Package Level 1 Gross Weight	8.81 kg 19.42 lb
Package Level 1 EAN	6417019244983

Technical

Conventional Free-air Thermal Current (I_{th})	$\Theta = 40\text{ °C}$ 400 A
Conventional Thermal Current (I_{the})	Fully Enclosed 400 A
Degree of Protection	acc. to IEC 60529 IP20
Fourth Pole Position	Right Side
Fourth Pole Type	Switched - With Solid Link
Fuse Size	NH0 NH1 NH2
Fuse System	DIN
Handle Type	Pistol handle
Mounting Type	Base mounting
Number of Poles	4P
Operating Mode	Front
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out, Bottom In - Top Out
Power Loss	at Rated Current 36 W
Rated Conditional Short-Circuit Current (I_{nc})	(500 V) 100 kA (690 V) 80 kA
Rated Current (I_n)	Main Circuit 400 A
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	1000 V
Rated Operational Current AC-21A (I_e)	(500 V) 400 A (690 V) 400 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A
Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 132 kW (400 V) 220 kW (415 V) 230 kW (500 V) 280 kW (690 V) 400 kW
Rated Operational Voltage	Main Circuit 690 V AC
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 14 kiloampere rms
Standards	IEC 60947-3
Switches Operating Mechanism	40 (Right Side)
Terminal Type	Lug terminals
Terminal Width	25 mm
Tightening Torque	30 ... 44 N·m

Technical UL/CSA

Tightening Torque	30 ... 44 N·m
-------------------	---------------

Certificates and Declarations

A2L Certificate – IEC	1SCC311209D0201
ATEX Certificate	No certification needed
CCC Certificate	CCC OS315-400 2016
Declaration of Conformity - CE	1SCC311099D2704
DNV GL Certificate	1SCC311131D0203
UL Certificate	No certification needed

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC001040 - Fuse switch disconnecter
ETIM 10	EC001040 - Fuse switch disconnecter
UNSPSC	39122233
IDEA Granular Category Code (IGCC)	5291 >> Fuse switch disconnecter
eClass	V11.1 : 27371401
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
E-Number (Finland)	3660758

Categories

Low Voltage Products and Systems → Switches → Switch Fuses

