



ENGLISH

## Datasheet

Stock No: 180-7161

# RS Pro Gas Detector, LED



	Detector	Transmitter
Frequency response	20 to 100kHz	40kHz
Operating temperature	0 to 50°C	0 to 50°C
Operating humidity	<80% RH	<80% RH

## Product Details

### Audio/Visual Gas/Air Leakage Detector

A ultrasonic detector designed to locate gas or air leaks which can be used with the transmitter to locate roof, wind-shield, gasket leaks, and the indication of pipes and conduits.

Visual bar LED display panel and audible indication

Requires 2 x PP3 batteries (stock no. [394-9059](#))

**Gases Detected:**

Non-specific

### Supplied with

full instructions; ear pieces; accessories suitable for use in awkward places; moulded case; instruction manual.

### Warning

Not designed to detect the leakage of flammable gas



ENGLISH

## Specifications:

Application	Conduit & Pipe Identification, Door & Window Leaks
Display Type	LED
Power Source	Battery
Battery Type	9V
Dimensions	255 x 70 x 28mm
Maximum Operating Temperature	+50°C
Model Number p	GS-5800
Minimum Operating Temperature	0°C
Height	28mm
Width	70mm
Length	255mm