

Mod. 3110HL.B

3110HL – EXPLORER CASES, ULTRALIGHT WATERPROOF CASE


Small size watertight case, injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products.

IP67 and MIL Stan certified to be resistant to impact, liquids, shocks.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Manual pressure release valve
- Soft rubber handle grip
- Certified to grant constant performances between -33°C and +90 °C.



METRIC MM-KG-C°

**INTERNAL DIMENSIONS**

L LENGTH	310 mm
W WIDTH	100 mm
D DEPTH	108 mm
LID	20 mm
BASE	88 mm


EXTERNAL DIMENSIONS

L LENGTH	336 mm
W WIDTH	159 mm
D DEPTH	127 mm

OTHER DATA

WEIGHT EMPTY	0.95 Kg
WEIGHT WITH FOAM	1.05 Kg
WEIGHT WITH CUSTOM FOAM	Kg
VOLUME	3.4 lt
BUOYANCY	2.5 Kg/max
OPERATING TEMPERATURE	°C min -33 / max 90

IMPERIAL IN-LBS-F°



INTERNAL DIMENSIONS

L LENGTH	12 3/16 in
W WIDTH	3 15/16 in
D DEPTH	4 1/4 in
LID	13/16 in
BASE	3 7/16 in

EXTERNAL DIMENSIONS

L LENGTH	13 1/4 in
W WIDTH	5 1/4 in
D DEPTH	5 in

OTHER DATA

WEIGHT EMPTY	2.09 lbs
WEIGHT WITH FOAM	2.31 lbs
WEIGHT WITH CUSTOM FOAM	lbs
VOLUME	0.89 gal
BUOYANCY	5.51 lbs/max
OPERATING TEMPERATURE	°F min -27.4 / max 194