



SCALANCE X308-2M; managed IE switch, compact; 4x 10/100/1000 Mbit/s for RJ45 ports electrical; 2x 100/1000 Mbit/s for 2-port media modules, electrical or optical; LED diagnostics; error signaling contact; select/set pushbutton; PROFINET IO device; network management; Integrated redundancy manager; office features (RSTP, VLAN, IGMP,...); C-PLUG in scope of supply.

product type designation	SCALANCE X308-2M
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	8
number of optical ports / maximum	4
interfaces / for communication / integrated	
number of electrical connections • for network components or terminal equipment	4
number of 10/100/1000 Mbit/s RJ45 ports / integrated • with securing collar	4
number of connectable media modules • with 2 ports	2
interfaces / other	
number of electrical connections • for signaling contact • for media module • for power supply	1 2 1
type of electrical connection • for signaling contact • for power supply	2-pole terminal block 4-pole terminal block
design of the removable storage • C-PLUG	Yes
signal inputs/outputs	
operating voltage / of the signaling contacts • at DC / rated value	24 V
operational current / of the signaling contacts • at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage supply / redundant power supply unit	No
type of voltage / 1 / of the supply voltage • supply voltage / 1 / rated value • power loss [W] / 1 / rated value • supply voltage / 1 / rated value • consumed current / 1 / maximum • type of electrical connection / 1 / for power supply • product component / 1 / fusing at power supply input • fuse protection type / 1 / at input for supply voltage	DC 24 V 16.6 W 18 ... 32 V 0.7 A 4-pole terminal block Yes F 3 A / 32 V
ambient conditions	

ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport note 	<p>-40 ... +70 °C</p> <p>-40 ... +70 °C</p> <p>-40 ... +70 °C</p> <p>Reduced operating temperature through the use of media modules (-40 °C to +70 °C) or SFP plug-in transceivers (-40 °C to +60 °C). If the device is installed in the vertical position, the maximum operating temperature is reduced to +50 °C.</p>
relative humidity	
<ul style="list-style-type: none"> at 25 °C / without condensation / during operation / maximum 	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	120 mm
height	125 mm
depth	124 mm
net weight	1.4 kg
fastening method	When used in shipbuilding, installation on a 35 mm standard mounting rail is not permitted.
<ul style="list-style-type: none"> 19-inch installation 35 mm top hat DIN rail mounting wall mounting S7-300 rail mounting S7-1500 rail mounting 	<p>No</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>No</p>
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of $\leq 0.3\text{ s}$	100
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
<ul style="list-style-type: none"> CLI web-based management MIB support TRAPs via email configuration with STEP 7 RMON port mirroring multiport mirroring CoS PROFINET IO diagnosis 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
PROFINET conformity class	B
product function / switch-managed	Yes
protocol / is supported	
<ul style="list-style-type: none"> Telnet HTTP HTTPS TFTP FTP BOOTP GMRP DCP LLDP SNMP v1 SNMP v2 SNMP v3 IGMP (snooping/querier) 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
identification & maintenance function	
<ul style="list-style-type: none"> I&M0 - device-specific information I&M1 - higher level designation/location designation 	<p>Yes</p> <p>Yes</p>
product functions / diagnostics	
product function	

<ul style="list-style-type: none"> port diagnostics 	Yes
<ul style="list-style-type: none"> statistics Packet Size 	Yes
<ul style="list-style-type: none"> statistics packet type 	Yes
<ul style="list-style-type: none"> error statistics 	Yes
<ul style="list-style-type: none"> SysLog 	Yes
product functions / VLAN	
product function	
<ul style="list-style-type: none"> VLAN - port based 	Yes
<ul style="list-style-type: none"> VLAN - protocol-based 	No
<ul style="list-style-type: none"> VLAN - IP-based 	No
<ul style="list-style-type: none"> VLAN dynamic 	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
protocol / is supported / GVRP	Yes
product functions / DHCP	
product function	
<ul style="list-style-type: none"> DHCP client 	Yes
<ul style="list-style-type: none"> DHCP Option 82 	Yes
<ul style="list-style-type: none"> DHCP Option 66 	Yes
<ul style="list-style-type: none"> DHCP Option 67 	Yes
product functions / redundancy	
product function	
<ul style="list-style-type: none"> ring redundancy 	Yes
<ul style="list-style-type: none"> High Speed Redundancy Protocol (HRP) 	Yes
<ul style="list-style-type: none"> high speed redundancy protocol (HRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> high speed redundancy protocol (HRP) with standby redundancy 	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> redundancy procedure STP 	Yes
<ul style="list-style-type: none"> redundancy procedure RSTP 	Yes
<ul style="list-style-type: none"> redundancy procedure MSTP 	Yes
<ul style="list-style-type: none"> Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	Yes
<ul style="list-style-type: none"> Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> passive listening 	Yes
protocol / is supported	
<ul style="list-style-type: none"> STP/RSTP 	Yes
<ul style="list-style-type: none"> STP 	Yes
<ul style="list-style-type: none"> RSTP 	Yes
<ul style="list-style-type: none"> MSTP 	Yes
<ul style="list-style-type: none"> RSTP big network support 	Yes
<ul style="list-style-type: none"> LACP 	Yes
product functions / security	
product function	
<ul style="list-style-type: none"> ACL - MAC-based 	Yes
<ul style="list-style-type: none"> ACL - port/MAC-based 	Yes
<ul style="list-style-type: none"> IEEE 802.1x (radius) 	Yes
<ul style="list-style-type: none"> broadcast/multicast/unicast limiter 	Yes
<ul style="list-style-type: none"> broadcast blocking 	Yes
protocol / is supported	
<ul style="list-style-type: none"> SSH 	Yes
product functions / time	
product function	
<ul style="list-style-type: none"> SICLOCK support 	Yes
protocol / is supported	
<ul style="list-style-type: none"> NTP 	Yes
<ul style="list-style-type: none"> SNTP 	Yes

<ul style="list-style-type: none"> • IEEE 1588 profile default 	Yes
standards, specifications, approvals	
standard	
<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Division 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 60950-1, CSA C22.2 No. 60950-1
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4:2007 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2:2005
MTBF	40 a
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 	KF
<ul style="list-style-type: none"> • according to IEC 81346-2:2019 	KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
standards, specifications, approvals / hazardous environments	
standard / for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • from CSA and UL 	UL 1604 and UL 2279-15 (Hazardous Location), CSA C22.2 No. 213-M1987, Class 1 / Division 2 / Group A, B, C, D / T4, Class 1 / Zone 2 / Group IIC / T4
certificate of suitability	
<ul style="list-style-type: none"> • CCC / for hazardous zone according to GB standard 	Yes; GB3836.1, GB3836.8
<ul style="list-style-type: none"> • CCC / for hazardous zone according to GB standard / as marking 	Ex nA IIC T4 Gc
standards, specifications, approvals / other	
certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
<ul style="list-style-type: none"> • C-Tick 	Yes
<ul style="list-style-type: none"> • KC approval 	Yes
<ul style="list-style-type: none"> • railway application in accordance with EN 50155 	No
standards, specifications, approvals / marine classification	
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) 	Yes
<ul style="list-style-type: none"> • French marine classification society (BV) 	Yes
<ul style="list-style-type: none"> • Det Norske Veritas (DNV) 	No
<ul style="list-style-type: none"> • Germanische Lloyd (GL) 	No
<ul style="list-style-type: none"> • DNV GL 	Yes
<ul style="list-style-type: none"> • Korean Register of Shipping (KRS) 	Yes
<ul style="list-style-type: none"> • Lloyds Register of Shipping (LRS) 	Yes
<ul style="list-style-type: none"> • Nippon Kaiji Kyokai (NK) 	Yes
<ul style="list-style-type: none"> • Polski Rejestr Statkow (PRS) 	No
<ul style="list-style-type: none"> • Royal Institution of Naval Architects (RINA) 	No
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAx-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial security concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial security measures that may be implemented, please visit https://www.siemens.com/industrialsecurity . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available

and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Security RSS Feed under <https://www.siemens.com/cert>. (V4.6)

Approvals / Certificates

EMC For use in hazardous locations



[ATEX-Zone 2-Declaration](#)



IECEX

[FM](#)

[CCC-Ex](#)



UL

Declaration of Conformity Test Certificates Marine / Shipping



EG-Konf.

[Manufacturer Declaration](#)



[Type Test Certificates/Test Report](#)



ABS



BUREAU VERITAS

Marine / Shipping



LRS

[NK / Nippon Kaiji Kyokai](#)



RINA



DNV-GL



KR

last modified:

11/9/2023