


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
H	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		INITIAL RELEASE	24NOV2009	RC	AH



LC CONN. MARK	LC CONN. MARK
A	B
B	A

NOTES:

- ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm OR 1300 nm ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
 - RETURN LOSS ≥ 20 dB, IN MATED CONDITION AGAINST REFERENCE CONNECTOR AT 850 nm OR 1300 nm
 - TEST RESULT SHEET IS SUPPLIED WITH EACH INDIVIDUAL PACKED ASSEMBLY
 - CABLE INFORMATION:
 - CORE DIAMETER: 50/125 μ m
 - OUTER JACKET DIAMETER: 1.8x3.6 mm
 - OUTER JACKET COLOUR: ORANGE
 - OUTER JACKET MATERIAL: LSZH
- BLANK LABEL

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061310-Y	XY.0

2	BLANK LABEL	3
2	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE	2
L	FOCAB 1.8MZ 50/125, ORANGE, LSZH	1
Qty	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC \pm - 1 PLC \pm - 2 PLC \pm - 3 PLC \pm - 4 PLC \pm - ANGLES \pm - FINISH -
MATERIAL - WEIGHT - CUSTOMER DRAWING		DWN R. COOLEN 16OCT2009 CHK A. HENGELMOLEN 16OCT2009 APVD A. HENGELMOLEN 16OCT2009 NAME Tyco Electronics Corporation 's-Hertogenbosch, Nederland FIBER OPTIC LEAD 1.8MZ LC/DPX - LC/DPX MULTI MODE 50/125 SIZE A2 CAGE CODE 00779 DRAWING NO. C=2061310 RESTRICTED TO - SCALE NTS SHEET 1 of 1 REV A

2061310