




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Mating Alignment: **With**
Mating Alignment Type: **Polarization**
Mating Retention: **With**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Contacts Preloaded	Yes
Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	32 VDC
-------------------	--------

Body Features

Primary Product Color	Red
-----------------------	-----



Contact Features

Contact Underplating Material	Nickel
Wire Contact Termination Area Plating Material	Nickel
Contact Layout	Inline
Contact Type	Socket
Contact Mating Area Plating Material	Gold (Au)
Contact Retention Within Housing	Without
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Latch
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Glass-Filled Thermoplastic
------------------	----------------------------

Dimensions

Connector Width	8.6 mm[.338 in]
Connector Height	23 mm[.905 in]
Connector Length	13.8 mm[.543 in]

Usage Conditions

Operating Temperature Range	-30 – 75 °C[-22 – 167 °F]
-----------------------------	---------------------------

Operation/Application

Halogen Free	Yes
Shielded	No
Circuit Application	Signal

Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------



UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	34
Packaging Method	Tube

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2432675-1
SDE RITS SOCKET ASSY



TE Part # 2217480-2
KIT, BTLI, SDE OPEN HEAD



TE Part # 2362810-1
SDE CRIMP HAND TOOL FRAME W /O DIES



TE Part # 1-1554809-3
RITS CONN. PLUG ASSY 3P RED COVER



TE Part # 1-1565994-3
RITS HDR ASSY R/A SMT TYPE 3P



TE Part # 2432675-2
SDE RITS SOCKET DIE ASSY



TE Part # 2217480-1
KIT, BTLI, SDE OPEN HEAD

Also in the Series | RITS Socket Connectors




Standard Rectangular Connectors(16)

Customers Also Bought



TE Part #1871418-1
DYNAMIC D-5800 REC HSG 4P WITH HTS CONN




TE Part #T2071244201-000
H24BP-T6-F DOCKING FRAME_FIXED




TE Part #2013285-3
DYNAMIC D-5 DYNATAP 20P ASSY DIN TYPE



TE Part #1473562-3
RITS CONN. PLUG ASSY 3P YELLOW DIN TYPE



TE Part #1473571-6
RITS.JUNCTION BOX 2D 6P P/M



TE Part #2316671-1
HD1 REC CONTACT AU0.38 S SIZE L/P



TE Part #1473565-3
RITS CONN.HDR ASSY 3P



TE Part #2-1903130-6
DYNAMIC 1200D TAB HSG 12P F/H BLACK Y



TE Part #T2071164101-000
H16BP-T4-M DOCKING FRAME_FLOATING



TE Part #2260110-1
MINI IO PIERCING CABLE ASSY L500



Documents

Product Drawings

RITS CONN. SOCKET ASSY 3P RED

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1746741-3_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1746741-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1746741-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

RITS Connector Interconnection System/e-CON Connector

Japanese

Instruction Sheet (non U.S.)

Japanese

HAND TOOL FOR RITS PLUG SOCKET ASSEMBLY

Japanese

Agency Approvals

UL Report

English