

# DWST83346-1

## TSTAK IP54 Deep Box

### Selling Propositions

- LOCKABLE - Via Padlock (Not Included) For Added Security
- HEAVY DUTY METAL FRONT LATCHES - increasing strength, durability and longevity
- METAL-PIN SIDE LATCHES - allowing TSTAK modules to be connected together. The metal pin design provides longer life
- IP54 WATERSEAL - Providing Water And Dust Protection To Tools And Fixings Inside The Box
- DEWALT TRACKER READY - Fixing point built into the TSTAK box to allow a DEWALT Tracker to be installed and the box tracked via DEWALT Tool Connect
- HALF SIZE INTERNAL TOTE TRAY - For Easy Access to Key Hand Tools, Fixings and Power Tool Accessories
- 30KG LOAD CAPACITY

### Standard Equipment

- HALF SIZE INTERNAL TOTE TRAY - For Easy Access to Key Hand Tools, Fixings and Power Tool Accessories

### Warranty specifications

- Standard Warranty

Specifications	
Width	440.0 mm
Depth	333.0 mm
Height	302.0 mm
Length	440.0 mm