


TIMKEN

The Timken Company
 4500 Mt Pleasant St. NW
 N. Canton, OH 44720
 Phone: (234) 262-3000
 E-Mail: CustomerCAD@timken.com • Web site: www.timken.com

Timken Part Number 3490 - 3420, Tapered Roller Bearings - TS (Tapered Single) Imperial

This is the most basic and most widely used type of tapered roller bearing. It consists of two main separable parts: the cone (inner ring) assembly and the cup (outer ring). It is typically mounted in opposing pairs on a shaft.



[Specifications](#) | [Dimensions](#) | [Abutment and Fillet Dimensions](#) | [Basic Load Ratings](#) | [Factors](#)

Specifications

Series	3400
Cone Part Number	3490
Cup Part Number	3420
Design Units	Imperial
Bearing Weight	1.40 lb 0.700 Kg
Cage Type	Stamped Steel

Dimensions

d - Bore	1.5 in 38.1 mm
D - Cup Outer Diameter	3.1250 in 79.375 mm

B - Cone Width	1.1721 in 29.771 mm
C - Cup Width	0.9375 in 23.813 mm
T - Bearing Width	1.1563 in 29.370 mm

Abutment and Fillet Dimensions

R - Cone Backface "To Clear" Radius¹	0.14 in 3.560 mm
r - Cup Backface "To Clear" Radius²	0.130 in 3.30 mm
da - Cone Frontface Backing Diameter	1.80 in 45.72 mm
db - Cone Backface Backing Diameter	2.05 in 52.07 mm
Da - Cup Frontface Backing Diameter	2.94 in 74.68 mm
Db - Cup Backface Backing Diameter	2.64 in 67.06 mm
Ab - Cage-Cone Frontface Clearance	0.05 in 1.3 mm
Aa - Cage-Cone Backface Clearance	0.04 in 1 mm
a - Effective Center Location³	-0.34 in -8.60 mm

Basic Load Ratings

C90 - Dynamic Radial Rating (90 million revolutions)⁴	6100 lbf 27100 N
C1 - Dynamic Radial Rating (1 million revolutions)⁵	23500 lbf 105000 N
C0 - Static Radial Rating	26800 lbf 119000 N
C_{a90} - Dynamic Thrust Rating (90 million revolutions)⁶	3820 lbf 17000 N

Factors

K - Factor⁷	1.6
e - ISO Factor⁸	0.37
Y - ISO Factor⁹	1.64
G1 - Heat Generation Factor (Roller-Raceway)	29.9
G2 - Heat Generation Factor (Rib-Roller End)	11.2
Cg - Geometry Factor	0.0781

¹ These maximum fillet radii will be cleared by the bearing corners.

² These maximum fillet radii will be cleared by the bearing corners.

³ Negative value indicates effective center inside cone backface.

⁴ Based on 90×10^6 revolutions L_{10} life, for The Timken Company life calculation method. C_{90} and C_{a90} are radial and thrust values.


⁵ Based on 1×10^6 revolutions L_{10} life, for the ISO life calculation method.

⁶ Based on 90×10^6 revolutions L_{10} life, for The Timken Company life calculation method. C_{90} and C_{a90} are radial and thrust values for a single-row, $C_{90(2)}$ is the two-row radial value.

⁷ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

⁸ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.

⁹ These factors apply for both inch and metric calculations. Consult your Timken representative for instruction on use.



IMPERIAL UNITS

ISO Factor - e	0.37
ISO Factor - Y	1.64
Bearing Weight	1.4 lb
Number of Rollers Per Row	15
Effective Center Location	-0.34 inch

TIMIKEN®

THE TIMKEN COMPANY
NORTH CANTON, OHIO USA

3490 - 3420
TS BEARING ASSEMBLY

K Factor	1.6
Dynamic Radial Rating - C90	6100 lbf
Dynamic Thrust Rating - Ca90	3820 lbf
Static Radial Rating - C0	26800 lbf
Dynamic Radial Rating - C1	23500 lbf

Every reasonable effort has been made to ensure the accuracy of the information contained in this writing, but no liability is accepted for errors, omissions or for any other reason.

FOR DISCUSSION ONLY