

KERN HN-D



"Pen type" hardness testing device in accordance with Leeb testing for mobile hardness testing of metals



Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	255 x 215 x 73 mm
Gross weight:	1,134 kg
Net weight:	160 g
Shipping method:	Parcel service
UN number:	3481

Construction

Dimensions (WxDxH):	22 x 35 x 147 mm
Dimensions housing (WxDxH):	22 x 35 x 147 mm
Overall dimensions mounted (WxDxH):	22 x 35 x 147 mm

Piktogramme

STANDARD



OPTION



Measuring system

Measuring capacity [Max]:	960
Measuring range (Min):	170
Precision (of [Max]):	1 %
Readability:	1
Sensor:	D
Weighing units:	HRC HRB HB HV HL

Display

Display digit height (large):	9 mm
Display digit height (small):	5 mm

Functions

All measurement directions possible (360°):	yes
Obtaining average:	yes
Statistical function:	yes
Wireless printer connection:	yes

Power supply

Charging time:	3 h
Input voltage:	100 - 240 V
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO
Operating time (Backlight off):	16 h

Services (optional)

Factory calibration certificate:	961-131
----------------------------------	---------

Category

Brand:	Sauter
Category:	Hardness testers
Product Group:	Electronic Leeb hardness tester