



fitted with

- work equipment**
- connected load**
- power consumption**
- system of protection**
- class of protection**
- technology**
- usage**
- luminaire body**
- material
- surface
- lamp cover**
- tubular sections**
- material
- surface
- balance of articulation joints**
- weight (net)**
- mains lead**

48 x Light-emitting diode
 neutral white, 3700-4200 K
 Color Rendering Index (CRI)=90
 electronic plug-in ballast
 100-240V; 50/60 Hz
 approx. 14 W
 IP 20
 II
 multi-stage switchable, continuously dimmable
 multi-function switch

plastic
 ESD-version
 screen, milky, Polyamide

tubular aluminum section
 ESD-coat of lacquer
 spring
 approx. 6.0 .b (2.7 kg)
 approx. 11.2 ft. (3.4 m); NEMA 1-15P plug

fastening

- lens; dimensions**
- lens material**
- lens; diopters**
- add-on lens; dimensions**
- special features**

screw-down flange
 Ø 6.3 in. (160 mm)
 glass
 3.5
 not available
 light characteristic can be adjusted with a three-way switch



NEMA 1-15P

illuminance

measuring conditions: d=15cm

Em: 3089 lx
Emax: 4636 lx
Emin: 1013 lx

