



1023-DC2

AMP-Superseal, 2 pin / set, male/Female

Product Properties:

Housing material	Polyamide (PA)
Connection type	Crimp
Rated current	14 A
Rated voltage	24 V
Contact material	Other
Surface treatment contacts	Tinned
Type of locking	Integrated in plug-in connector
Degree of protection (IP)	IP67
Model	Other
Pole codification	1, 2
Number of connections per pole	1 .
Max. continuous temperature resistance contact part	-40-125 °C
Max. continuous temperature resistance strain relief	-40-125 °C

Dimensions:

Connection cross section (solid-core)	1.5 mm ²
Connection cross section (fine-strand)	1.5 mm ²
Width	17 mm
Height	9.3 mm
MOQ	1 .
Unit	pcs
Rated voltage	24 V
Length	42 mm

Approvals:

Degree of protection (IP)	IP67
---------------------------	------

Compliance:

Conflict Minerals	Contain "Tin"
Iron and Steel Sanction	Contain no Iron or Steel
REACH	No SVHC (241 Subs. 27 June 2024)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)

Other information:

ETIM-Class	EC002560 - Plug-in connector for plug-in building installation
ETIM-Release	9.0
Product Group	AMP Superseal
Search Description	AMP SUPERSEAL 1.5
Alternative SKU	1023-DC2

Logistic information:

Barcode	733117612821
Country of origin	TW
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	1023-DC2
Taric code	85122000
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.