

# KSB32CP15D

Tap off unit, Canalis KS 100A to 1000A, 8 modules of 18mm, 32A, DIN rail, 3L+N+PE, 1 Schuko + 1 industrial power sockets



## Main

Range of product	Canalis
Product name	KS
Product or component type	Tap-off unit
Product compatibility	Modular device
[Ie] rated operational current	32 A at 35 °C
Tap-off unit socket description	Domestic 10/16A 2P+T 230V
Tap-off unit 2nd socket description	Industrial 16A 3P+N+T 415V
Tap-off unit polarity	3L+N+PE
Provided equipment	Blanking plate
Colour	White (RAL 9001)

## Complementary

Device application	Power socket distribution Low power distribution
[Ue] rated operational voltage	230...690 V depending on protective device
[Uimp] rated impulse withstand voltage	6.8 kV
[Ui] rated insulation voltage	400 V depending on protective device 500 V depending on protective device 690 V depending on protective device
Network frequency	50/60 Hz
Protection type	Without protection
Tap-off unit disconnection mode	By drawing out
Tap-off unit connector type	With phase selection
Standards	IEC 60439-2 IEC 61439-6
Body material	Plastic
Number of 18mm modules	8
Width	437.5 mm
Depth	108 mm
Height	165 mm
Net weight	3 kg

## Environment

Earthing system	TT - busbar trunking TN-S - busbar trunking TN-C - busbar trunking TT - tap-off unit TN-S - tap-off unit
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins