

Servo motor EMMT-AS-40-M-LS-R2M

Part number: 8171417

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Ambient temperature	-40 °C ... 40 °C
Note on ambient temperature	Up to 80°C with derating of -2.25% per degree Celsius
Max. installation height	4000 m
Note on max. installation height	As of 1,000 m: only with derating of -1.0% per 100 m
Storage temperature	-40 °C ... 70 °C
Relative air humidity	0 - 90%
Conforms to standard	IEC 60034
Temperature class as per EN 60034-1	F
Max. winding temperature	155 °C
Rating class as per EN 60034-1	S1
Temperature monitoring	Digital motor temperature transmission via EnDat® 2.2
Motor type to EN 60034-7	IM V1 IM V3
Mounting position	Any
Degree of protection	IP40
Note on degree of protection	IP67 for motor housing including connection components
Concentricity, coaxiality, axial runout to DIN SPEC 42955	N
Balance quality	G 2.5
Detent torque	<1.0% of peak torque
Bearing lifetime under nominal conditions	20000 h
Interface code, motor out	40P
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connector system	M23x1
Electrical connection 1, number of connections/cores	15
Electrical connection 1, connection pattern	00995913
Pollution degree	2
Note on materials	RoHS compliant
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Approval	RCM c UL us - Recognised (Oil)
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive

Feature	Value
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK regulations for electrical equipment
Certificate issuing authority	UL E342973
Nominal operating voltage DC	325 V
Type of winding switch	Star inside
Number of pole pairs	5
Standstill torque	0.45 Nm
Nominal torque	0.32 Nm
Peak torque	1.41 Nm
Nominal rotary speed	7000 rpm
Max. rotational speed	11800 rpm
Max. mechanical speed	15000 rpm
Angular acceleration	$\leq 100000 \text{ rad/s}^2$
Nominal power rating of motor	234 W
Continuous stall current	1.6 A
Nominal motor current	1.2 A
Peak current	6 A
Motor constant	0.267 Nm/A
Standstill torque constant	0.32 Nm/A
Voltage constant, phase-to-phase	19.3 mVmin
Phase-phase winding resistance	7.96 Ohm
Phase-phase winding inductance	9.8 mH
Winding longitudinal inductivity Ld (phase)	3.8 mH
Winding cross inductivity Lq (phase)	4.9 mH
Electric time constant	1.24 ms
Thermal time constant	21.4 min
Thermal resistance	1.35 K/W
Measuring flange	200 x 200 x 15 mm, steel
Total mass moment of inertia of output	0.07 kgcm ²
Product weight	700 g
Permissible axial shaft load	30 N
Permissible radial shaft load	150 N
Rotor position sensor	Absolute encoder, multi-turn
rotor position sensor, manufacturer designation	EQI 1131
rotor position sensor, absolute detectable revolutions	4096
Rotor position encoder interface	EnDat 22
Rotor position sensor, encoder measuring principle	Inductive
rotor position sensor, DC operating voltage	5 V
rotor position sensor, DC operating voltage range	3.6 V ... 14 V
rotor position sensor, position values per revolution	524288
Rotor position transducer resolution	19 bit
rotor position sensor, system accuracy of angle measurement	-120 arcsec ... 120 arcsec
Mean time to failure (MTTF), subcomponent	190 years, rotor position encoder