




**Part Number :** [2157601042](#)  
**Product Description :** Micro-Fit+ Versa Color  
Right-Angle Header, Through Hole, 3.00mm  
Pitch, Single Row, 2 Circuits, Matte Tin (Sn)  
Plating, Glow-Wire Capable, Yellow  
**Series Number :** 215760  
**Status :** Active  
**Product Category :** PCB Headers and  
Receptacles



Documents & Resources

**Drawings**  
[2157601042\\_sd.pdf](#)

**3D Models and Design Files**  
[2157601042\\_stp.zip](#)

**Specifications**  
[2064600001-AS-000.pdf](#)  
[2064600000-PS-000.pdf](#)  
[2064600001-TS-000.pdf](#)  
[2157590005-TS-000.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Compliant with Exemption 44; 33                                                       |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                        |
| REACH SVHC         | Not Contained per D(2024)6225-DC<br>(07 Nov 2024)                                     |
| EU RoHS            | Compliant per EU 2015/863                                                             |

- Multiple Part Product Compliance Statements
- Eu RoHS
  - REACH SVHC
  - Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|                |                                                                                                                                                  |
|----------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                                                           |
| Category       | PCB Headers and Receptacles                                                                                                                      |
| Series         | 215760                                                                                                                                           |
| Description    | Micro-Fit+ Versa Color Right-Angle Header, Through Hole, 3.00mm Pitch, Single Row, 2 Circuits, Matte Tin (Sn) Plating, Glow-Wire Capable, Yellow |
| Application    | Power, Wire-to-Board                                                                                                                             |
| Component Type | PCB Header                                                                                                                                       |
| Product Name   | Micro-Fit+ Versa Color                                                                                                                           |
| UPC            | 196823367526                                                                                                                                     |

#### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
|-----|---------|

#### Electrical

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 13.0A            |
| Voltage - Maximum             | 600V AC (RMS)/DC |

#### Physical

|                                |        |
|--------------------------------|--------|
| Breakaway                      | No     |
| Circuits (Loaded)              | 2      |
| Circuits (maximum)             | 2      |
| Color - Resin                  | Yellow |
| Durability (mating cycles max) | 25     |
| First Mate / Last Break        | No     |

|                                |                        |
|--------------------------------|------------------------|
| Flammability                   | 94V-0                  |
| Glow-Wire Capable              | Yes                    |
| Keying to Mating Part          | Yes                    |
| Lock to Mating Part            | Yes                    |
| Material - Metal               | High Copper Alloy      |
| Material - Plating Mating      | Matte Tin              |
| Material - Plating Termination | Matte Tin              |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 0.408/g                |
| Number of Rows                 | 1                      |
| Orientation                    | Right Angle            |
| Packaging Type                 | Tray                   |
| PC Tail Length                 | 3.17mm                 |
| PCB Retention                  | Yes                    |
| PCB Thickness - Recommended    | 1.57mm                 |
| Pitch - Mating Interface       | 3.00mm                 |
| Pitch - Termination Interface  | 3.00mm                 |
| Polarized to Mating Part       | Yes                    |
| Polarized to PCB               | Yes                    |
| Shrouded                       | Yes                    |
| Temperature Range - Operating  | -40° to +125°C         |
| Termination Interface Style    | Through Hole           |

---

## Mates With / Use With

### Mates with Part(s)

| Description                               | Part Number   |
|-------------------------------------------|---------------|
| Micro-Fit+ Single Row Receptacle Housings | <u>215759</u> |