




Fibre optic through-beam sensor

FE-00-M-V-E3



Application		
Function principle	Through-beam sensor	
Application	High temperature resistance; Robust design for use in harsh industrial environments; Resistant to various aggressive chemicals	
Detection zone		
Range with fibre-optic amplifier type	OCF; OKF; OOF; OUF	
OCF (High Power)		
Range of fibre optics	[mm]	1200
OKF		
Range of fibre optics	[mm]	120
OOF		
Range of fibre optics	[mm]	400
OUF		
Range of fibre optics	[mm]	120
Operating conditions		
Ambient temperature	[°C]	-20...150
Mechanical data		
Weight	[g]	95.5
Version of sensing head	straight	
Sensing head diameter	[mm]	3

E20492



Fibre optic through-beam sensor

FE-00-M-V-E3

Sensing head length	[mm]	10
Total length	[mm]	600
Min. bending radius	[mm]	20
Fibre arrangement		
Fibre material		glass
Fibre head material		stainless steel (1.4305 / 303)
Fibre sheath material		metal silicone

Accessories

Items supplied	E20103
----------------	--------

Remarks

Pack quantity	1 pcs.
---------------	--------