


Geberit Mapress Stainless Steel reducer with plain end (FKM, blue)



Example image

APPLICATION PURPOSES

- For chemicals and technical liquids
- For district heating water ≤ 140 °C
- For thermal media (solar)
- For mineral and lubricating oil
- For motor fuels (e.g. diesel)
- For compressed air (oil purity class 0–4)

- For solar technology, industry and shipbuilding
- For industrial gases (e.g. acetylene, shielding gases)

- Seal ring made of FKM, blue
- Pressing socket with black protection plug

CHARACTERISTICS

- Pressing indicator
- Concentric
- Silicone-free (LABS-free)

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	d1, ø mm	L cm	H cm
50133	15 / 12	18	15	5.5	3.5
50134	20 / 12	22	15	5.9	3.9
50135	20 / 15	22	18	5.7	3.7
50136	25 / 12	28	15	6.6	4.6
50137	25 / 15	28	18	6.4	4.4

Art. no.	DN	d, ø mm	d1, ø mm	L cm	H cm
50138	25 / 20	28	22	6	3.9
50141	32 / 20	35	22	7.1	5
50142	32 / 25	35	28	6.8	4.5
50145	40 / 20	42	22	8.2	6.1
50146	40 / 25	42	28	8.3	6
50147	40 / 32	42	35	7.7	5.1
50150	50 / 20	54	22	9.5	7.4
50151	50 / 25	54	28	11	8.7
50152	50 / 32	54	35	10.6	8
50153	50 / 40	54	42	9.2	6.2
50164	65 / 50	76.1	54	14.6	11.1
50167	80 / 50	88.9	54	16.2	12.8
50168	80 / 65	88.9	76.1	16.1	10.8

<i>Art. no.</i>	<i>DN</i>	<i>d, ø mm</i>	<i>d1, ø mm</i>	<i>L cm</i>	<i>H cm</i>
50169	100 / 50	108	54	17.2	13.7
50171	100 / 65	108	76.1	18.4	13.1
50172	100 / 80	108	88.9	20.3	14.3