



MULTIMASTER MM 700

Max Top

Oscillating multi-tool – MM 700

Our best MultiTool for the most rapid work progress in interior work and renovation with 60 accessories – from sawing in wood, metal and plastics, to cutting out tiles, cutting silicone joints and carpets, removing adhesive residues and tile adhesive.

Product number: 7 229 68 61 00 0

Details

- › Anti-vibration system: continuously safe and pleasant working thanks to minimal vibrations and outstanding noise insulation.
- › StarlockMax tool mounting: more work progress and greater precision thanks to 100% power transmission without losses.
- › QuickIN: tool changes in less than 3 seconds thanks to the patented tool-free FEIN rapid clamping system.
- › With the StarlockMax tool mounting, you can access around 180 FEIN accessories from the Starlock, Starlock Plus and StarlockMax performance classes.
- › 450 W FEIN high-power motor: high-power motor with a high copper content, which is suited to continuous use and overload for maximum cutting speed and the most rapid work progress.
- › Tacho generator: constant speeds even under load and infinitely variable electronic speed control.
- › Metal gearbox: ability to withstand high loading and outstanding service life because all the gearbox parts are made from metal.
- › Mechanical interface: for stationary operation in the table or drill jig holder or for securing the depth stop.
- › Industrial cable: large working radius thanks to finely stranded 5 metre rubber cable of industrial quality.

Price includes

- ✓ 2 E-Cut standard saw blades curved (35 mm)
- ✓ 1 E-Cut Precision BIM saw blade (35 mm)
- ✓ 1 E-Cut long-life saw blade (10 mm)
- ✓ 1 E-Cut long-life saw blade (32 mm)
- ✓ 1 E-Cut carbide Pro saw blade (32 mm)
- ✓ 1 carbide saw blade (diameter 75 mm)
- ✓ 1 Stopper knife
- ✓ 1 Multi-function knife
- ✓ Sanding sheets, perforated (10 each of grit 60, 80, 120, 180)
- ✓ 1 plastic carrying case
- ✓ 2 E-Cut standard saw blades curved (65 mm)
- ✓ 1 E-Cut Precision BIM saw blade (35 mm)
- ✓ 2 E-Cut long-life saw blades (35 mm)
- ✓ 1 E-Cut long-life saw blade (42 mm)
- ✓ 1 segmented saw blade (Ø 85 mm)
- ✓ 1 HM rasp (triangular)
- ✓ 1 Cutter blade, mushroom shaped
- ✓ 1 Sanding plate with holes
- ✓ 1 dust extraction device

Product feature

- ✓ Mechanical interface

Technical data

TECHNICAL DATA

Input	450 W
Output	250 W
Oscillations	10,000 - 19,500 rpm
Tool Holder	StarlockMax
Tool change	QuickIN
Amplitude	2 x 2,0°
Cable with plug	5 m
Weight according to EPTA	1.60 kg

VIBRATION AND SOUND EMISSION VALUES

Sound pressure level LpA
Uncertainty of measured value
KpA

85 dB
3 dB

Sound power level LWA
Uncertainty of measured value
KWA

96 dB
3 dB

Sound peak value
LpCpeak
Uncertainty of measured value
KpCpeak

97 dB
3 dB

Application examples

