




GE
Lighting



261
kWh/1000h

B
energy class

3
lumens/watt

Multi -Mirror® Quartzline® Projection - MR16

ELC / 500 24V 250W 1/10

15377

Product information

An extensive range of Specialist projector lamps which are precisely manufactured, with tailored filaments optimising source brightness giving high performance in many applications. -High light-generating efficacy to help reduce power consumption and heat generation- Prefocus-type caps or precision rim mounting to position the filament accurately in relation to the optics.

Application areas

 Other



Product data

Product Code	15377
Bulb Shape	Mirrored reflector
Bulb Diameter [mm]	11.1
Maximum Overall Length [mm]	44.5
Net weight per piece [g]	24
Gross weight per piece [g]	47
Brand	General Electric (GE)
Cap/Base	GX5.3

Performance data

Nominal center beam candlepower (CBCP) [cd]	67000
Weighted energy consumption [kWh/1000h]	260.77
Energy efficiency class (EEC)	B
Rated Life [h]	500
Nominal correlated colour temperature (CCT) [K]	3300
Nominal lumens [lm]	800
Colour Rendering Index (CRI) [Ra]	100

Electrical data

Coil type	CC-6
Ballast Required	Yes
Nominal power [W]	250
Nominal lamp voltage [V]	24

Logistic data

DUN Code	20043168153779
EAN Code	0043168153775
Pack Quantity	10
Layer quantity	220 EUR, 300 UK
Layer quantity EUR	220
Layer quantity UK	300
Pallet quantity EUR (PC)	1760
Pallet quantity UK (PC)	2400
Outer case size	135 x 131 x 304 (mm)
Product status	Available

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Entertainment Solution Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[High-res images / Technical drawings \(HTTP\)](#)

[Certificate for the Quality Management System of GE Lighting EMEA \(PDF\)](#)

[Certificate for the Environmental Management System of GE Lighting EMEA \(PDF\)](#)

Disclaimer

Special purpose lamp – Photographic. Not suitable for household illumination.