










PSZRON








HEAD **Reduced Head** TYPE **Open End** SECTION **Round** SURFACE **Linear Knurls**

 <i>M</i>	 <i>l</i>	 <i>g</i>	DESCRIPTION	 <i>d_h</i>	 <i>d_k</i>	 <i>k</i>	<i>d</i>	BULK PACK		SMALL PACK		 /1,000 kg
								ARTICLE	BOX QTY	ARTICLE	BOX QTY	
mm	mm	mm		mm	mm	mm	mm					kg
M3	9.8	0.5 - 2.5	PSZRON-03025	5.0	5.8	0.6	4.9	48491	10,000	48492	500	0.8
M4	10.3	0.5 - 3.0	PSZRON-0430	6.0	6.8	0.6	5.9	33036	10,000	33042	500	0.9
M5	11.8	0.5 - 3.0	PSZRON-0530	7.0	7.8	0.6	6.9	33049	10,000	33048	500	1.4
M6	14.3	0.5 - 3.0	PSZRON-0630	9.0	9.8	0.6	8.9	33047	4,000	33046	500	3.0
M8	15.8	0.5 - 3.0	PSZRON-0830	11.0	11.8	0.6	10.9	33240	2,000	33239	250	4.4
M10	19.8	0.8 - 3.5	PSZRON-1035	12.0	13.3	0.8	11.9	33242	2,000	33241	200	6.0



PSZRO

HEAD **Reduced Head** TYPE **Open End** SECTION **Round**

 <i>M</i>	 <i>l</i>	 <i>g</i>	DESCRIPTION	 <i>d_h</i>	 <i>d_k</i>	 <i>k</i>	<i>d</i>	BULK PACK		SMALL PACK		 /1,000 kg
								ARTICLE	BOX QTY	ARTICLE	BOX QTY	
mm	mm	mm		mm	mm	mm	mm					kg
M4	10.8	0.5 - 3.0	PSZRO-0430	6.1	6.5	0.5	6.0	00363	10,000	08856	500	1.1
M5	12.0	0.5 - 3.0	PSZRO-0530	7.1	7.5	0.5	7.0	33380	5,000	09659	500	1.6
	15.0	3.0 - 5.5	PSZRO-0555					33382	4,000	33381	500	1.8
M6	14.5	0.5 - 3.0	PSZRO-0630	9.1	9.5	0.5	9.0	00364	3,000	08530	500	3.4
	16.5	3.0 - 5.5	PSZRO-0655					33385	2,500	33384	500	3.7
M8	16.0	0.5 - 3.0	PSZRO-0830	11.1	11.5	0.5	11.0	00366	2,000	08937	250	5.0
	18.5	3.0 - 5.5	PSZRO-0855					33387	1,500	33386	250	5.5
M10	19.5	0.8 - 3.5	PSZRO-1035	12.5	12.9	0.5	12.4	33389	1,250	33388	250	6.7

M=Thread Size; *l*=Nominal Body Length; *g*=Grip Range (Min - Max); *d_h*=Hole Size; *d_k*=Nominal Head Diameter; *k*=Nominal Head Thickness; *d*=Nominal Barrel Diameter