




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
 © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
BD	48					AD REV PER EC 0420-0036-96	14 OCT 96	PF
						AE OBS -60 PER EC 0420-141-96	17 SEPT 97	SB



- 1 FOR MINI-APPLICATOR AND STRIPPER CRIMPER.
- 2 FOR HAND TOOL USE ONLY.
- 3 FOR STANDARD APPLICATOR PART #566184 ONLY.
- 4. WIRE RANGE OF 24-28, INSULATION RANGE OF .030-.040.
- 5. GOLD PLATING MAY NOT APPEAR ON CARRIER STRIP.
- 6 GOLD PLATING PER MIL-G-45204, NICKEL PLATING PER QQ-N-290, TIN PLATING PER MIL-T-10727, COPPER PLATING PER MIL-C-14550.
- 7 PLATED WITH .000050 GOLD OVER .000050 NICKEL.
- 8 PLATED WITH .000030 GOLD IN LOCALIZED GOLD PLATE AREA, GOLD FLASH ON REMAINDER, OVER .000050 NICKEL.
- 9 PLATED WITH GOLD FLASH OVER .000030 NICKEL.
- 10 PLATED WITH .000100-.000200 TIN.
- 11 PLATED WITH .000050 GOLD IN LOCALIZED GOLD PLATE AREA, GOLD FLASH ON REMAINDER, OVER .000050 NICKEL.
- 12 PLATED WITH .000030 GOLD IN LOCALIZED GOLD PLATE AREA, GOLD FLASH IN AREA FG, TIN PLATED WIRE BARRELS, OVER .000050 NICKEL.
- 13 PLATED WITH GOLD FLASH IN LOCALIZED GOLD PLATE AREA AND AREA FG, TIN PLATED WIRE BARRELS, OVER .000030 NICKEL.
- 14 PLATED WITH .000015 GOLD IN LOCALIZED GOLD PLATE AREA, GOLD FLASH ON REMAINDER, OVER .000050 NICKEL.
- 15 AMP ITALY PART NUMBER ONLY.
- 16 .000001 MIN GOLD IN LOCALIZED PLATE AREA AND AREA FG, .000030 MIN TIN OR TIN-LEAD ON WIRE BARRELS, ALL OVER .000030 MIN NICKEL.

	STANDARD	12	3	STRIP	6-66507-3
	STANDARD	16	1	STRIP	6-66507-2
OBSOLETE	STANDARD	13	3	STRIP	6-66507-1
OBSOLETE	SMALL PACK	8	2	LOOSE PIECE	6-66507-0
	STANDARD	13	2	LOOSE PIECE	5-66507-9
	STANDARD	12	2	LOOSE PIECE	5-66507-7
OBSOLETE	STANDARD	14	1	STRIP	5-66507-5
	STANDARD	13	1	STRIP	3-66507-1
	STANDARD	12	1	STRIP	3-66507-0
	STANDARD	11	1	STRIP	2-66507-8
	STANDARD	11	3	STRIP	2-66507-7
OBSOLETE	STANDARD	10	1	STRIP	1-66507-4
	STANDARD	9	3	STRIP	1-66507-3
	STANDARD	8	3	STRIP	1-66507-2
	STANDARD	9	2	LOOSE PIECE	1-66507-0
	STANDARD	8	2	LOOSE PIECE	66507-9
	STANDARD	7	2	LOOSE PIECE	66507-8
	STANDARD	9	1	STRIP	66507-4
	STANDARD	8	1	STRIP	66507-3
	STANDARD	7	1	STRIP	66507-2

PACKAGING TYPE	FINISH	USE	TYPE	PART NUMBER
----------------	--------	-----	------	-------------

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON : 2 PL DEC ± - 3 PL DEC ± .005 ANGLES ± -	DR 9-9-86 S. WELDON	AMP INCORPORATED Harrisburg, Pa. 17105		
	CHK 9-9-86 C. RICHARD			
MATERIAL BRASS PER MIL-C-50	APPD 9-10-86 L. BREKOSKY	NAME PIN CONTACT, SIZE 20 DF, 24-28 AWG, W/.030-.040 DIA INSULATION SUPPORT		
	APPD 9-10-86 V. KUMAR			
FINISH 6 SEE TABLE	PRODUCT SPEC	SIZE C	FSCM NO 00779	DRAWING NO 66507
	APPLICATION SPEC 114-10000	SCALE 10:1		SHEET 1 OF 1
WEIGHT	-			