

Eaton 157859

Catalog Number: 157859

Eaton Moeller® series P-SOL Undervoltage release, delayed, 230V50/60Hz, 240V50/60Hz



General specifications

Product Name	Catalog Number
Eaton Moeller® series P-SOL Accessory	157859
Undervoltage Release	EAN
	4015081544493
Product Length/Depth	Product Height
68 mm	90 mm
Product Width	Product Weight
24 mm	0.138 kg
Compliances	
CE	

Features & Functions

Electric connection type

Screw connection

Fitted with:

Internal delay for bridging intermittent voltage dips and fluctuations

Functions

Delayed

General

Application

Residential buildings

Utility buildings

Product category

Accessories

Product category

Accessories

Suitable for

Off-load switch

Voltage type

AC

Climatic environmental conditions

Ambient operating temperature - min

-25 °C

Ambient operating temperature - max

60 °C

Terminal capacities

Terminal capacity (solid/flexible with ferrule)

1 x (0,75 - 2,5) mm²

2 x (0.75 - 2.5) mm²

Terminal capacity (solid/stranded AWG)

1 x (18 - 14)

2 x (18 - 14)

Electrical rating

Rated operational voltage (Ue) at AC - min

230 V

Rated operational voltage (Ue) at AC - max

240 V

Magnet system

Pick-up voltage

0.85 - 1.1 V x Uc

Rated control supply voltage (Us) at AC, 50 Hz - min

0 V

Rated control supply voltage (Us) at AC, 50 Hz - max

230 V

Rated control supply voltage (Us) at AC, 60 Hz - min

0 V

Rated control supply voltage (Us) at AC, 60 Hz - max

240 V

Rated control supply voltage (Us) at DC - min

0 V

Rated control supply voltage (Us) at DC - max

0 V

Contacts

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

0

Number of contacts (normally open contacts)

0

Power consumption

Power consumption, pick-up, 50 Hz

3 VA, Pull-in power, Coil in a cold state and 1.0 x Us

Power consumption, pick-up, 60 Hz

3 VA, Pull-in power, Coil in a cold state and 1.0 x Us

Power consumption, sealing, 50 Hz

3 VA, Coil in a cold state and 1.0 x Us

Power consumption, sealing, 60 Hz

3 VA, Coil in a cold state and 1.0 x Us

Design verification

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Rated operational current for specified heat dissipation (I_n)

0 A

Static heat dissipation, non-current-dependent P_{vs}

0.8 W

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Resources

Catalogs

[Product Range Catalog Switching and protecting motors](#)

[Switching and protecting motors - catalog](#)

Characteristic curve

[eaton-motorstarters-undervoltage-sol30-fireman's-switch-characteristic-curve.eps](#)

Declarations of conformity

[DA-DC-00004206.pdf](#)

[DA-DC-00004069.pdf](#)

[DA-DC-00004851.pdf](#)

[DA-DC-00003914.pdf](#)

[DA-DC-00004230.pdf](#)

[DA-DC-00004787.pdf](#)

Drawings

[eaton-manual-motor-starters-release-u-pkz0-accessory-dimensions.eps](#)

[eaton-manual-motor-starters-release-u-pkz0-accessory-3d-drawing.eps](#)

eCAD model

[DA-CE-ETN.P-SOL-XUV\(230V50_60HZ,240V50_60HZ\)](#)

mCAD model

[DA-CD-a_pkz](#)

[DA-CS-a_pkz](#)

Wiring diagrams

[eaton-manual-motor-starters-undervoltage-u-pkz0-accessory-wiring-diagram.eps](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia