



Part Number : [673298020](#)

Product Description : Universal Serial Bus (USB) Shielded I/O Receptacle, Type A, Single Upright Right-Angle, Solder Tail Length 2.00mm, 3.65mm Beveled Metal Pins, PCB Thickness 1.60mm, Gold (Au) Flash, Lead-Free

Series Number : 67329

Status : Active

Product Category : I/O Connectors



Documents & Resources

Drawings

[673298020_sd.pdf](#)

[PK-67329-001-001.pdf](#)

3D Models and Design Files

[673298020_stp.zip](#)

[EE-67329-001-001.pdf](#)

Specifications

[PS-89485-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	67329
Description	Universal Serial Bus (USB) Shielded I/O Receptacle, Type A, Single Upright Right-Angle, Solder Tail Length 2.00mm, 3.65mm Beveled Metal Pins, PCB Thickness 1.60mm, Gold (Au) Flash, Lead-Free
Application	Wire-to-Board
Comments	Standard Mount Type, Beveled Metal Pin Length: 3.65mm
Component Type	Receptacle
Product Name	USB
Standard	USB 2.0
Type	A
UPC	822350416900

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.0A
-------------------------------	------

Shielded	Yes
Shield Type	Full Shield

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Female
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Mounting Style	Upright
Net Weight	1.937/g
Number of Rows	4
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	2.00mm
Pitch - Mating Interface	N/A
Pitch - Termination Interface	1.40mm
Plating min - Mating	0.102µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Termination Interface Style	Through Hole
Waterproof / Dustproof	No

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	USB Type A Plug

This document was generated on Jul 09, 2025