




Connectors > Connector Accessories > Connector Hardware



Hardware Accessory Function: **Coding & Keying**

Connector Hardware Accessory Type: **Keying Plug**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Hardware Accessory Function	Coding & Keying
Connector Hardware Accessory Type	Keying Plug

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156



TE Part # CAT-103156-RECHS
Connector Housing, Rectangular, 3.96 mm, 1 Row

Also in the Series | SL-156



Connector Contacts(23)



Connector Hardware(4)



Insertion & Extraction Tools(1)




Power Contacts(13)



Rectangular Connector Housings(150)



Rectangular Power Connectors(147)



Wire-to-Board Connector Assemblies & Housings(146)

Customers Also Bought



TE Part #61988-1
250 FASTON REC 22-18 AWG BR



TE Part #5-87631-2
60 MODIV HSG DR MRKD .100 POL



TE Part #175149-2
AMP UNIVE. POWER CONN TAB
CONT




TE Part #175150-1
UNIVERSAL POWER CONN TAB
CONT



TE Part #175150-2
AMP UNIVE. POWER CONN TAB
CONT



TE Part #454575-4
BLADE, SHEAR



TE Part #454709-1
ANVIL INSERT



TE Part #1-640250-8
18P SL156 HSG W/LCK RAMP NATL



TE Part #2217206-4
Blade, Slug



TE Part #690569-1
FRONT SHEAR PLATE

Documents

Product Drawings

[KEYING PLUG .045 SQ PST CONN BLK](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_640254-2_K_c-640254-2-k.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_640254-2_K_c-640254-2-k.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_640254-2_K_c-640254-2-k.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English