



Main

Range of product	Easy9
Product or component type	Residual current circuit breaker (RCCB)
Device short name	Easy9 RCCB
Poles	2P
Neutral position	Left
[In] rated current	100 A
Network type	AC
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Rated breaking and making capacity	500 A
Rated conditional short-circuit current	Easy9 MCB: 3000 A 100 A

Complementary

Device location in system	Outgoer
Network frequency	50/60 Hz
[Ue] rated operational voltage	127/230 V AC 50/60 Hz
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	440 V AC
[Uimp] rated impulse withstand voltage	4 kV
Contact position indicator	Yes
Control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top: YES
9 mm pitches	4
Height	82 mm
Width	36 mm
Depth	72 mm
Net weight	195 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	Grey (RAL 7035)
Mechanical durability	5000 cycles
Electrical durability	AC: 2000 cycles 230 V AC 50/60 Hz
Connections - terminals	Tunnel type terminal (top or bottom) 1...35 mm ² rigid Tunnel type terminal (top or bottom) 1...25 mm ² flexible
Tightening torque	3.5 N.m top or bottom

Environment

Standards	IEC 61008-1 BS EN 61008-1
Product certifications	ISI CE
Pollution degree	2 conforming to BS EN 61008-1
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

Contractual warranty

Warranty	18 months
----------	-----------