

# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 1000 V, nominal current: 32 A, number of connections: 4, connection method: Push-in connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.2 mm<sup>2</sup> - 6 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: black

## Your advantages

- The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- The compact design and front connection enable wiring in a confined space
- In addition to the testing option in the double function shaft, all terminal blocks provide an additional test pick-off
- Tested for railway applications

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1291898       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 100 pc        |
| Sales key                            | BE2313        |
| Product key                          | BE2313        |
| GTIN                                 | 4063151524869 |
| Weight per piece (including packing) | 12.15 g       |
| Weight per piece (excluding packing) | 12 g          |
| Customs tariff number                | 85369010      |
| Country of origin                    | CN            |

# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>

## Technical data

### Notes

#### General

|      |                                                                                              |
|------|----------------------------------------------------------------------------------------------|
| Note | The max. load current must not be exceeded by the total current of all connected conductors. |
|------|----------------------------------------------------------------------------------------------|

### Product properties

|                       |                                |
|-----------------------|--------------------------------|
| Product type          | Multi-conductor terminal block |
| Product family        | PTV                            |
| Area of application   | Railway industry               |
|                       | Machine building               |
|                       | Plant engineering              |
|                       | Process industry               |
| Number of connections | 4                              |
| Number of rows        | 1                              |
| Potentials            | 1                              |

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Maximum power dissipation for nominal condition | 1.02 W |
|-------------------------------------------------|--------|

### Connection data

|                                                                                           |                                                              |
|-------------------------------------------------------------------------------------------|--------------------------------------------------------------|
| Number of connections per level                                                           | 4                                                            |
| Nominal cross section                                                                     | 4 mm <sup>2</sup>                                            |
| Stripping length                                                                          | 9 mm ... 11 mm                                               |
| Internal cylindrical gage                                                                 | A4                                                           |
| Connection in acc. with standard                                                          | IEC 60947-7-1                                                |
| Conductor cross section rigid                                                             | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>                    |
| Cross section AWG                                                                         | 24 ... 10 (converted acc. to IEC)                            |
| Conductor cross section flexible                                                          | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>                    |
| Conductor cross section, flexible [AWG]                                                   | 24 ... 10 (converted acc. to IEC)                            |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>                    |
| Flexible conductor cross section (ferrule with plastic sleeve)                            | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>                    |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                  |
| Nominal current                                                                           | 32 A                                                         |
| Maximum load current                                                                      | 38 A (with 6 mm <sup>2</sup> conductor cross section, rigid) |
| Nominal voltage                                                                           | 1000 V                                                       |
| Nominal cross section                                                                     | 4 mm <sup>2</sup>                                            |

# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>

## Connection cross sections directly pluggable

|                                                                   |                                            |
|-------------------------------------------------------------------|--------------------------------------------|
| Conductor cross section rigid                                     | 0.75 mm <sup>2</sup> ... 6 mm <sup>2</sup> |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 1.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>  |
| Flexible conductor cross section (ferrule with plastic sleeve)    | 1.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>  |

## Ex data

### Rated data (ATEX/IECEx)

|                                                    |                                     |
|----------------------------------------------------|-------------------------------------|
| Identification                                     | Ex II 2 G Ex eb IIC Gb              |
| Operating temperature range                        | -60 °C ... 110 °C                   |
| Ex-certified accessories                           | 1088748 D-PTV 2,5/4-QUATTRO         |
|                                                    | 1083618 DS-PTV 2,5/4                |
|                                                    | 3047196 ATP-UT-QUATTRO              |
|                                                    | 1212587 SF-SL 0,6X3,5-100 S-VDE     |
|                                                    | 3022276 CLIPFIX 35-5                |
| List of bridges                                    | Plug-in bridge / FBS 2-6 / 3030336  |
|                                                    | Plug-in bridge / FBS 3-6 / 3030242  |
|                                                    | Plug-in bridge / FBS 4-6 / 3030255  |
|                                                    | Plug-in bridge / FBS 5-6 / 3030349  |
|                                                    | Plug-in bridge / FBS 10-6 / 3030271 |
|                                                    | Plug-in bridge / FBS 20-6 / 3030365 |
|                                                    | Plug-in bridge / FBS 50-6 / 3032224 |
| Bridge data                                        | 27 A (4 mm <sup>2</sup> )           |
| Ex temperature increase                            | 40 K (27,6 A / 4 mm <sup>2</sup> )  |
| for bridging with bridge                           | 550 V                               |
| - At bridging between non-adjacent terminal blocks | 550 V                               |
| - At cut-to-length bridging                        | 275 V                               |
| - At cut-to-length bridging with cover             | 275 V                               |
| - At cut-to-length bridging with partition plate   | 550 V                               |
| Rated insulation voltage                           | 500 V                               |
| output                                             | (Permanent)                         |

### Ex level General

|                      |                           |
|----------------------|---------------------------|
| Rated voltage        | 550 V                     |
| Rated current        | 27 A (4 mm <sup>2</sup> ) |
| Maximum load current | 31 A (6 mm <sup>2</sup> ) |
| Contact resistance   | 0.7 mΩ                    |

### Ex connection data General

|                              |                                           |
|------------------------------|-------------------------------------------|
| Nominal cross section        | 4 mm <sup>2</sup>                         |
| Rated cross section AWG      | 12                                        |
| Connection capacity rigid    | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup> |
| Connection capacity AWG      | 24 ... 10                                 |
| Connection capacity flexible | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup> |
| Connection capacity AWG      | 24 ... 10                                 |

# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 6.2 mm  |
| End cover width    | 2.2 mm  |
| Height             | 69.2 mm |
| Depth              | 45.7 mm |
| Depth on NS 35/7,5 | 47.2 mm |
| Depth on NS 35/15  | 54.7 mm |

## Material specifications

|                                                                  |                  |
|------------------------------------------------------------------|------------------|
| Color                                                            | black (RAL 9005) |
| Flammability rating according to UL 94                           | V0               |
| Insulating material group                                        | I                |
| Insulating material                                              | PA               |
| Static insulating material application in cold                   | -60 °C           |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C           |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3      |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3      |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3      |
| Fire protection for rail vehicles (DIN EN 45545-2) R26           | HL 1 - HL 3      |
| Surface flammability NFPA 130 (ASTM E 162)                       | passed           |
| Specific optical density of smoke NFPA 130 (ASTM E 662)          | passed           |
| Smoke gas toxicity NFPA 130 (SMP 800C)                           | passed           |

## Electrical tests

### Surge voltage test

|                                                |             |
|------------------------------------------------|-------------|
| Result                                         | Test passed |
| Short-time withstand current 4 mm <sup>2</sup> | 0.48 kA     |
| Result                                         | Test passed |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 2.2 kV      |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>

## Test for conductor damage and slackening

|                                |                              |
|--------------------------------|------------------------------|
| Rotation speed                 | 10 rpm                       |
| Revolutions                    | 135                          |
| Conductor cross section/weight | 0.2 mm <sup>2</sup> / 0.2 kg |
|                                | 4 mm <sup>2</sup> / 0.9 kg   |
|                                | 6 mm <sup>2</sup> / 1.4 kg   |
| Result                         | Test passed                  |

## Environmental and real-life conditions

### Aging

|                    |             |
|--------------------|-------------|
| Temperature cycles | 192         |
| Result             | Test passed |

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |                                                |
|------------------------|------------------------------------------------|
| Specification          | DIN EN 50155 (VDE 0115-200):2018-05            |
| Spectrum               | Long life test category 2, bogie-mounted       |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level              | 6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz      |
| Acceleration           | 3.12g                                          |
| Test duration per axis | 5 h                                            |
| Test directions        | X-, Y- and Z-axis                              |
| Result                 | Test passed                                    |

### Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Pulse shape                    | Half-sine                         |
| Acceleration                   | 30g                               |
| Shock duration                 | 18 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |
| Result                         | Test passed                       |

### Ambient conditions

|                                          |                                                                                                                              |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                                                    |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                                                                              |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                                                                              |
| Permissible humidity (operation)         | 20 % ... 90 %                                                                                                                |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                                                                                |

## Standards and regulations

# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>

|                                  |
|----------------------------------|
| Connection in acc. with standard |
|----------------------------------|

|               |
|---------------|
| IEC 60947-7-1 |
|---------------|

## Mounting

|               |
|---------------|
| Mounting type |
|---------------|

|           |
|-----------|
| NS 35/7,5 |
|-----------|

|          |
|----------|
| NS 35/15 |
|----------|

# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>

## Drawings

Circuit diagram



# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1291898>

| CSA<br>Approval ID: 158887 |                       |                       |                   |                             |
|----------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                | 600 V                 | 30 A                  | 26 - 10           | -                           |
| Use group C                | 600 V                 | 30 A                  | 26 - 10           | -                           |
| Use group D                | 600 V                 | 5 A                   | 26 - 10           | -                           |

| CB<br>IECEE CB Scheme<br>Approval ID: DE1-67139 |                       |                       |                   |                             |
|-------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                 | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                 | 1000 V                | 32 A                  | -                 | 0.2 - 6                     |

| EAC<br>Approval ID: RU C-DE.BL08.B.00644 |  |  |  |  |
|------------------------------------------|--|--|--|--|
|------------------------------------------|--|--|--|--|

| cULus Recognized<br>Approval ID: E60425 |                       |                       |                   |                             |
|-----------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                         | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                             | 600 V                 | 30 A                  | 26 - 10           | -                           |
| Use group C                             | 600 V                 | 30 A                  | 26 - 10           | -                           |
| Use group F                             | 1000 V                | 30 A                  | 26 - 10           | -                           |

| VDE Zeichengenehmigung<br>Approval ID: 40056318 |                       |                       |                   |                             |
|-------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                 | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                 | 1000 V                | 32 A                  | -                 | 0.2 - 6                     |

| IECEx<br>Approval ID: IECExPTB20.0037U |  |  |  |  |
|----------------------------------------|--|--|--|--|
|----------------------------------------|--|--|--|--|

# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>



**ATEX**

Approval ID: PTB20ATEX1016U



**CCC**

Approval ID: 2021122313114374



**UKCA-EX**

Approval ID: CSAE 22UKEX1099U



**EAC Ex**

Approval ID: KZ 7500525010101950

# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PTV 4-QUATTRO BK - Feed-through terminal block



1291898

<https://www.phoenixcontact.com/gb/products/1291898>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)