




Part Number : [3000817502](#)
Product Description : MX150 Pass-Through
Unsealed Receptacle, Dual Row, 6 Circuits,
Stackable, Keying Option B, UL 94 HB, Black
Housing
Series Number : 300081
Status : Active
Product Category : Connector Housings
Engineering Number : 100062-0565



Documents & Resources

Drawings
[3000817502_sd.pdf](#)

Specifications
[3000810000-AS-000.pdf](#)
[3000810000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	300081
Description	MX150 Pass-Through Unsealed Receptacle, Dual Row, 6 Circuits, Stackable, Keying Option B, UL 94 HB, Black Housing
Application	Pass-Through, Power, Wire-to-Wire, Automotive
Product Name	MX150
UPC	196823756702

Physical

Circuits (maximum)	6
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.955/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarization	B
Polarized to Mating Part	Yes
Stackable	Yes
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150 Pass-Through Sealed Connector, Panel Mount, Dual Row, 12 Circuits, Keying Option A, UL 94 HB, Black Housing, Single Seal	<u>3000817001</u>
MX150 Pass-Through Sealed Connector, Panel Mount, Dual Row, 12 Circuits, Keying Option A, UL 94 HB, Black Housing, Dual Seal	<u>3000817101</u>

Use with Part(s)

Description	Part Number
MX150 Female Terminals	<u>33001</u>