




Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**

Insertion & Extraction Tool Application: **Contact-to-Wire**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Wire

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability















Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 962867-1 4,0MM RECEPTACLE CONTACT	 TE Part # 965844-1 4MM BUCHSENKONTAKT	 TE Part # 962953-1 4MM SOCKET CONTACT SWS LOOSE PIECE	 TE Part # 965846-1 4MM BUCHSENKONTAKT
 TE Part # 9-965839-1 4,0 DIA ABS PIN ASS	 TE Part # 962957-1 4MM BU-KONTAKT EDS	 TE Part # 962955-1 4MM SOCK.CONT.(LP)	 TE Part # 965840-1 4MM BUCHSENKONTAKT
 TE Part # 9-965844-1 4,0 DIA ABS SOC.ASS	 TE Part # 965865-1 4MM PIN CONTACT	 TE Part # 965861-1 4MM BUCHSENKONTAKT	 TE Part # 1703420-2 DIA 4MM CON
 TE Part # 965839-1 4MM PIN CONTACT	 TE Part # 965841-1 4MM PIN CONTACT	 TE Part # 963788-1 BUCHS-KONTAKT 4,0MM	 TE Part # 962953-2 4MM SOCKET CONTACT SWS



TE Part # 965843-1
4MM CONTACT PIN

TE Part # 962957-2
4MM BU-KONTAKT EDS

TE Part # 9-965845-1
4,0 DIA ABS PIN ASS

TE Part # 965857-1
4MM PIN CONTACT LOOSE PIECE

Also in the Series | Round Connector System

Automotive Connector Caps & Covers
(5)

Automotive Housings(12)

Automotive Terminals(48)

Connector Seals & Cavity Plugs(5)

DIN Connectors(3)

Insertion & Extraction Tools(8)

Customers Also Bought

TE Part #CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS

TE Part #CAT-C73765-M1E
M12 Field Installable Unshielded

TE Part #K1126416
Relay 29-011-12A

TE Part #DTM04-6P-E004
REC, 6P, BLK, N

TE Part #DT04-3P
REC, 3P, GRY, N

TE Part #927779-3
JPT REC 2.8 Contact SRC Sn (LP)



Documents

Product Drawings

ASSEMBLY TOOL

English

Datasheets & Catalog Pages

CRIMPING TERMINALS

English

CRIMPING WHERE FORM MEETS FUNCTION

English