



**Part Number :** 5054321601

**Product Description :** 1.25mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Dual Row, Positive Lock, 16 Circuits, Black

**Series Number :** 505432

**Status :** Active

**Product Category :** Connector Housings



## Documents & Resources

### Drawings

[5054321601\\_sd.pdf](#)

3D Models and Design Files

[5054321601.dxf](#)

[5054321601\\_stp.zip](#)

### Specifications

[5054320000-AS-000.pdf](#)

[5054329200-200.pdf](#)

[5054320000-002.pdf](#)

[5054320000-005.pdf](#)

[5054320000-006.pdf](#)

[5054321000-PS-002.pdf](#)

[5054321000-PS-006.pdf](#)

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant                                      |
| China RoHS         | ⓘ<br>per SJ/T 11365-2006                          |
| EU ELV             | Compliant per 2000/53/EC                          |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                |
| REACH SVHC         | Not Contained per D(2024)7663-DC<br>(21 Jan 2025) |

|         |                           |
|---------|---------------------------|
| EU RoHS | Compliant per EU 2015/863 |
|---------|---------------------------|

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

|              |   |
|--------------|---|
| Status       | Active  |
| Category     | Connector Housings  |
| Series       | 505432  |
| Description  | 1.25mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Dual Row, Positive Lock, 16 Circuits, Black |
| Application  | Signal, Wire-to-Board   |
| Product Name | Micro-Lock Plus   |
| UPC          | 889056422222  |

### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

### Physical

|                    |            |
|--------------------|------------|
| Circuits (maximum) | 16         |
| Color - Resin      | Black      |
| Gender             | Receptacle |

|                               |                |
|-------------------------------|----------------|
| Glow-Wire Capable             | No             |
| Keying to Mating Part         | None           |
| Lock to Mating Part           | Yes            |
| Material - Resin              | Polyester      |
| Net Weight                    | 356.750/mg     |
| Number of Rows                | 2              |
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 1.25mm         |
| Pitch - Termination Interface | 1.25mm         |
| Polarized to Mating Part      | Yes            |
| Temperature Range - Operating | -40° to +105°C |

## Mates With / Use With

### Mates with Part(s)

| Description   | Part Number   |
|---|---------------|
| 1.25mm Pitch Micro-Lock Plus Vertical, Dual Row, Surface Mount Headers    | <u>505433</u> |
| 1.25mm Pitch Micro-Lock Plus Right-Angle, Dual Row, Surface Mount Headers | <u>505448</u> |

### Use with Part(s)

| Description  | Part Number      |
|--|------------------|
| Pre-Crimped Lead Micro-Lock Plus Female-to-Micro-Lock Plus Female, Tin (Sn) Plating, 150.00mm Length, 26 AWG, Black  | <u>797581148</u> |
| Pre-Crimped Lead Micro-Lock Plus Female-to-Micro-Lock Plus Female, Tin (Sn) Plating, 300.00mm Length, 26 AWG, Black  | <u>797581149</u> |
| Pre-Crimped Lead Micro-Lock Plus Female-to-Micro-Lock Plus Female, Gold (Au) Plating, 150.00mm Length, 26 AWG, Black | <u>797582143</u> |

|  |                  |
|--|------------------|
| Pre-Crimped Lead Micro-Lock Plus Female-to-Micro-Lock Plus Female, Gold (Au) Plating, 300.00mm Length, 26 AWG, Black | <u>797582144</u> |
| Micro-Lock Plus Female Crimp Terminals   | <u>505431</u>    |

---

This document was generated on Jul 10, 2025