



Cut protection

KRYTECH 585

Moderate risk - ISO C



CUT PROTECTION
LEVEL C



CATEGORY 2



ISO 13997:

13 N

DEXTERITY

EN420:
5/5



Enhanced safety, comfort and durability with Grip & Proof Technology

SPECIFIC ADVANTAGES



Cut protection

- Optimal cut resistance



Comfort

- A seamless plaited glove and an optimized coating covering for a maximum comfort, dexterity and flexibility.



Durability

- Optimal durability that offers better productivity and optimizes your costs



Productivity

- Grip and Proof coating ensures an excellent grip in very oily environment . It also reduces muscle strain and boosts productivity



Skin protection

- Free of harmful substances: DMF Free



Washability

- Washable up to 3 times at 60°C , allowing to extend glove lifespan, reduce costs and waste.



Practical

- Cut level easy to identify thanks to the marking on the back of the glove.

INDUSTRIES

- Automotive/mechanical industry
- Food industry
- Construction Industry (Metalworkers/Locksmiths)
- Other industries
- Plastics industry
- Manufacturing

APPLICATIONS

- Handling and installing metal structures
- Maintenance and work in cold stores
- Handling heavy parts with cut risk
- Cutting & stamping heavy metal sheets
- Post-injection material removal
- Maintenance in wet or cold environments
- Road works in cold conditions
- Finishing sharp parts
- Handling metal parts
- Handling parts post-press




Cut protection

KRYTECH 585

Moderate risk - ISO C

LEGENDS



PRODUCT DETAILS

Interior finish	Seamless textile support from HDPE fibres
Gauge	15
Exterior finish	Ventilated back
Material	Nitrile GRIP&PROOF coating
Cuff characteristic	Knitted Cuff
Colour.s	Black Grey
European sizes	7 8 9 10 11
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	2.7E+10 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	3.0E+11 Ω

LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 48 pairs/carton
-----------	---

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/05/18/0907
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE