



Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dichromium tris(chromate) (1% in 4734965198) Dodecamethylcyclohexasiloxane (D6) (.5% in 27519759152) Decamethylcyclopentasiloxane (D5) (.5% in 27519759152) Pb (4% in Component Part) Octamethylcyclotetrasiloxane (D4) (.5% in 27519759152) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 1-1587987-3
RECEPTACLE ASSEMBLY, 250A, MSD



TE Part # 1587987-9
RECEPTACLE ASSEMBLY, 250A, MSD

Customers Also Bought



TE Part #1-1718628-1
AMP MCP 2.8 HSG. 4POS.,ASS'Y



TE Part #66740-2
TYPE XII FEMALE CONT (L.P.)



TE Part #DTM04-08PA
REC, 8P, GRY, N, A




TE Part #CX7205-000
RHW-48/12-1200/ADH-0



TE Part #66261-1
MALE CONTACT ASSY. (L.P.)



TE Part #5-1618398-0
EV100AAANA=CONTACTOR, SPST-NO 9-36Vdc



TE Part #284716-3
6 POS REC. CONNECTOR FOR MTII



TE Part #1-1718628-1
AMP MCP 2.8 HSG. 4POS.,ASS'Y



TE Part #7-1579008-6
UNLOCKING TOOL



TE Part #1-1625999-4
HSC100 1R0 5%

Documents

Product Drawings
Plug Assembly, 250A, MSD
English

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_2103212-9_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2103212-9_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2103212-9_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English