

RoHS Compliant

3150 SERIES D-SUB SOLDER TYPE FEMALE

REV	DATE	DESCRIPTION	ECN NO.	NAME
A	96.04.23	NEW RELEASE		DEAN
B	00.12.22	△ MODIFIED DIM	AK0012007	CLOUDY
C	01.03.06	△ MODIFICATION	I0102031	TINA
D	02.02.16	△ ADD COLOR	AK0201007	AUTUMN
E	03.12.20	△ MODIFICATION	AK0312024	ZHYING
F	04.09.20	△ MODIFICATION	AK0409026	XZ

MATERIAL

HOUSING : THERMOPLASTIC (UL94V-0)




TERMINAL : COPPER ALLOY

TERMINAL PLATING : SEE ORDER INFORMATION

SHELL : COPPER ALLOY

SHELL PLATING : SEE ORDER INFORMATION

RS P/N	Shell Size	Dimension					
		A	B	C	D	E	F
4883770	09F	16.33	24.99	30.81	19.28	7.900	10.72
4883792	15F	24.66	33.32	39.25	27.75	7.900	10.72
4883815	25F	38.38	47.04	53.03	41.30	7.900	10.72
4883821	37F	54.84	63.50	69.50	57.40	7.900	10.72



ORDER INFORMATION

* 3150-** F * * * * *

△ "G":GREEN PRODUCT

△ "G":GREEN PRODUCT

09 25

15 37

19 50

23

F:FEMALE

B:BLACK

W:WHITE

U:BLUE

△ J:DARK RED 235C

" ":PE PACKAGING

"1":TRAY PACKAGING

O:WITH #4-40 HEX. NUTS IN FRONT OF SHELL
& USE RIVET TO PLUG THE HOLES.(H:5.8mm)

X:WITHOUT NUT

F1:1u" min. Au PLATED

S1:1u" min. Au IN CONTACT AREA.

△ Sn/Pb (OR Sn FOR G3150-**F**S1**)

IN SOLDER TAIL AREA

Z:Zn YELLOW

T:Sn

N:Ni

GENERAL TOLERANCE ±0.25mm GENERAL ANGLE TOLERANCE ±3° ⊕	PART NO.: RS - * * * * *	
	DRAWN BY	DEAN(WST)
	CHECKED BY	CHYN
	APPROVED BY	△ KEVIN
	SORTING NO.	P1009,P1025 (WST)
DRAWING NO. △ *3150-**F*****		DRAWING SIZE
UNIT		mm
PAGE		1 OF 1

ISSUED

[ARTICLE:044033 V4]