





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			P3	REVISED PER ECO-11-004587	11MAR11	RK	HMR

- ① HOUSING: FLAME RETARDANT, THERMOPLASTIC, BLACK
POST: BRASS
- ② POINT OF MEASUREMENT FOR PLATING THICKNESS
- ③ THE NOTED DIMENSIONS APPLY FROM THE BASIC
DIMENSION LINE (NOT THE POST CENTERLINE)
TO THE SURFACE INDICATED
- ④ ON ASSEMBLIES WITH FOUR OR MORE POSITIONS,
TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS,
ONE POLARIZATION SLOT.
- 5 FOR USE WITH .062±.008 PRINTED CIRCUIT BOARD
- ⑥ .000030 GOLD IN THE CONTACT AREA,
.000100-.000200 MATTE TIN-LEAD ON THE
SOLDER TAIL, ALL OVER .000050 NICKEL
- ⑦ .000030 GOLD IN THE CONTACT AREA,
.000100-.000200 MATTE TIN ON THE
SOLDER TAIL, ALL OVER .000050 NICKEL
- ⑧ HIGH TEMPERATURE CONFIGURATION.
- ⑨ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

OBSOLETE 9	8	7	2.600	2.520	2.400	24	25	7-103904-4	
			2.500	2.420	2.300	23	24	7-103904-3	
			2.400	2.320	2.200	22	23	7-103904-2	
			2.300	2.220	2.100	21	22	7-103904-1	
			2.200	2.120	2.000	20	21	7-103904-0	
			2.100	2.020	1.900	19	20	6-103904-9	
			2.000	1.920	1.800	18	19	6-103904-8	
			1.900	1.820	1.700	17	18	6-103904-7	
			1.800	1.720	1.600	16	17	6-103904-6	
			1.700	1.620	1.500	15	16	6-103904-5	
1.600			1.520	1.400	14	15	6-103904-4		
1.500			1.420	1.300	13	14	6-103904-3		
1.400			1.320	1.200	12	13	6-103904-2		
1.300			1.220	1.100	11	12	6-103904-1		
1.200			1.120	1.000	10	11	6-103904-0		
1.100			1.020	.900	9	10	5-103904-9		
1.000			.920	.800	8	9	5-103904-8		
.900			.820	.700	7	8	5-103904-7		
.800			.720	.600	6	7	5-103904-6		
.700			.620	.500	5	6	5-103904-5		
.600			.520	.400	4	5	5-103904-4		
.500			.420	.300	3	4	5-103904-3		
.400			.320	.200	2	3	5-103904-2		
.300			.220	.100	1	2	5-103904-1		
9 OBSOLETE			6	2.600	2.520	2.400	24	25	2-103904-4
9 OBSOLETE				2.500	2.420	2.300	23	24	2-103904-3
9 OBSOLETE				2.400	2.320	2.200	22	23	2-103904-2
9 OBSOLETE				2.300	2.220	2.100	21	22	2-103904-1
9 OBSOLETE				2.200	2.120	2.000	20	21	2-103904-0
9 OBSOLETE				2.100	2.020	1.900	19	20	1-103904-9
9 OBSOLETE	2.000	1.920		1.800	18	19	1-103904-8		
9 OBSOLETE	1.900	1.820		1.700	17	18	1-103904-7		
9 OBSOLETE	1.800	1.720		1.600	16	17	1-103904-6		
9 OBSOLETE	1.700	1.620		1.500	15	16	1-103904-5		
6-103904-2	1.600	1.520	1.400	14	15	1-103904-4			
	1.500	1.420	1.300	13	14	1-103904-3			
	1.400	1.320	1.200	12	13	1-103904-2			
	1.300	1.220	1.100	11	12	1-103904-1			
	1.200	1.120	1.000	10	11	1-103904-0			
	1.100	1.020	.900	9	10	103904-9			
	1.000	.920	.800	8	9	103904-8			
	.900	.820	.700	7	8	103904-7			
	.800	.720	.600	6	7	103904-6			
	.700	.620	.500	5	6	103904-5			
	.600	.520	.400	4	5	103904-4			
	.500	.420	.300	3	4	103904-3			
	.400	.320	.200	2	3	103904-2			
	.300	.220	.100	1	2	103904-1			
	REMARKS	PLATING	D	C	B	A	NO OF POS	ASSEMBLY PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 5-17-93 E. BRANDBERG CHK 5-17-93 J. GESFORD		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		NAME HEADER ASSY, AMPMODU MTE, RIGHT ANGLE, SINGLE ROW, .100CL .025 SQ POSTS, WITH LATCH & HOLD DOWNS	
		APVD — PRODUCT SPEC 108-25034 APPLICATION SPEC —		SIZE CAGE CODE DRAWING NO A1 00779 C-103904	
MATERIAL 		FINISH SEE TABLE		RESTRICTED TO —	
		WEIGHT —		SCALE 4:1 SHEET 1 OF 1 REV B3	
CUSTOMER DRAWING					