



POLINOX non-woven mounted grinding wheel PNZ dia. 80x50 mm shank dia. 6 mm A100 for fine grinding and finishing

POLINOX non-woven mounted grinding wheel PNZ dia. 80x50 mm shank dia. 6 mm A100 for fine grinding and finishing

Item number: [44658080](#)

EAN: [4007220157176](#)

POLINOX mounted grinding wheels consist of non-woven polyamide abrasive, into which abrasive grain is integrated. The non-woven abrasive material is arranged in multiple radial flaps, with abrasive cloth interlayers. This flap structure facilitates improved stock removal and achieves a coarser surface finish.

Technical information

Abrasive	Aluminium oxide A
Dia. external	80 mm
Dia. shank	6 mm
Grit size	100
Length, shank	40
Max. RPM	7500 RPM
PFERD TOOLS type	PNZ 8050/6 A 100
RPM, optimum	4000 RPM
Width	50 mm

Advantages

- ✔ Highly flexible, enabling optimal adjustment to the contour.
- ✔ Cool grinding and low thermal load on the workpiece.
- ✔ The open structure and high flexibility of the non-woven material prevents tool clogging.

Recommendations for use

- ✓ For the best results, use at a recommended cutting speed of 10-20 m/s. This provides an ideal compromise between stock removal rate, surface quality, thermal load on the workpiece and tool wear.

Safety notes

- ✓ The maximum permitted peripheral speed is 32 m/s.
- ✓ For safety reasons, the maximum permitted rotational speed indicated must never be exceeded.

Materials that can be worked

- ✓ Aluminium
 - ✓ Brass
 - ✓ Bronze
 - ✓ Cast steel
 - ✓ Cobalt-based alloys
 - ✓ Copper
 - ✓ Fibre-reinforced thermosetting plastics (GRP, CRP)
 - ✓ Hardened, heat-treated steels over 1.200 N/mm² (< 38 HRC)
 - ✓ Nickel-based alloys (e.g. Inconell and Hastelloy)
 - ✓ Stainless steel (INOX)
 - ✓ Steel materials with a hardness > 54 HRC
 - ✓ Steels up to 1,200 N/mm² (< 38 HRC)
 - ✓ Thermoplastics
 - ✓ Titanium
 - ✓ Titanium alloys
 - ✓ Zinc
-

Applications

- ✓ Cleaning
 - ✓ Deburring
 - ✓ Roughening
 - ✓ Step-by-step fine grinding
 - ✓ Structuring (matt finishing, brush matting and satin finishing)
 - ✓ Surface work
-

Drive types

- ✓ Drive spindle
 - ✓ Flexible shaft drive
 - ✓ Straight grinder
-



August Rüggeberg GmbH & Co. KG
Hauptstraße 13
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

info@pferd.com