

Product data sheet

Specifications



Undervoltage release, Acti9 iMN, 115VAC

A9A26959

Main

range of product	Acti9
Product or component type	Undervoltage release
Device short name	iMN
[Uc] control circuit voltage	115 V AC 400 Hz
Control type	Standard
9 mm pitches	2

Complementary

Range compatibility	Acti9 iC60H RCBO Acti9 iC60H RCBO PoN Acti9 iC60H2 RCBO Acti9 iC60N RCBO Acti9 iKQE RCBO Acti9 iCVm40 Acti9 iCVr40 Acti9 iDDm40
Local signalling	Action indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top and bottom: YES
Width	18 mm
Colour	White
Connections - terminals	Clamp terminal - 1 cable(s) 7 mm ² - rigid Clamp terminal - 2 cable(s) 2.6 mm ² - rigid Clamp terminal - 1 cable(s) 5 mm ² - flexible Clamp terminal - 2 cable(s) 2.6 mm ² - flexible with cable end
Tightening torque	1 N.m

Environment

Standards	EN/IEC 60947-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	8 cm
Package 1 Length	9.3 cm
Package 1 Weight	78 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	8.8 cm
Package 2 Width	10 cm
Package 2 Length	26.6 cm
Package 2 Weight	679 g
Unit Type of Package 3	S03
Number of Units in Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	6.604 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	1 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.5 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0.5 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.1 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	Yes
SCIP Number	148451a0-e477-4625-8a90-921d761437d5
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
Halogen-free status	Product contains halogen above thresholds
Silicone-free	No

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	29
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins