

# Cig-Arrete CSA-FDW24



The weatherproof **CSA-FDW24** is designed for the detection of unauthorised smoking in external areas and will detect a flame lighting a cigarette with 120 degree field of view. The module is designed for single applications, and will detect a 25mm cigarette lighter flame at 6 metres within 1 second. This system is specifically designed to be installed outdoors and carries a IP65 rating. Typical applications include open areas, building entry/exit points, used in hospital entrances, ambulance bays, factory gates, reception areas, school shelters and many more public places. Fully programmable with a simple hand held remote **CSA-IR2**.

- Plays pre-programmed voice files
- Housed in a Ip65 weatherproof box
- Can be powered by 24Vdc or AA batteries
- Up to 100 messages can be programmed
- Selectable time delays between messages
- Hi-Resolution voice playback
- Used in hospital entrances, ambulance bays, factory gates, reception areas, school shelters and many more public places.

## Product Features

Time delays between messages are selectable via the remote programmer to ensure that the message is broadcast at the right time.


Up to 100 messages can be pre-programmed and selected either individually or sequentially where each message in the list is played in turn on each activation.

Contains a Windows® based file structure which allows simple 'drag and drop' file copying for ease of programming. New SmartWave® hi-resolution voice playback software produces crystal clear hi-fidelity audio files to be broadcast in any location.

Cig-Arrête® SD Evolution units can be powered simply by 8-28Vdc or by 4 x AA batteries (not supplied)

**Dimensions** 198L x 152.5W x 76.2H mm

**Weight** 0.73kg



**ALL** of the SD Evolution units require a CSA-IR2 remote control.

One CSA-IR2 can control multiple units. You **do not** need one remote per unit.



**Hoyles Electronic Developments Ltd**

T. 01744 886600

F. 01744 886607

E. sales@hoyles.com

W. www.hoyles.com