


FEATURES

- **Annealed Copper Conductor:** Provides superior conductivity and strength
- **Polyvinyl Chloride Jacket:** Offers excellent insulation and protection against environmental factors
- **Plain Conductor Type:** Ensures easy installation and consistent performance
- **30/0.25 Core Strands:** Enhances flexibility and durability
- **Temperature Range -15 °C to 90 °C:** Suitable for diverse operating environments
- **500 V Voltage Rating:** Ideal for medium voltage applications
- **9.4 mm Outside Diameter:** Compact design for efficient space utilisation

RS PRO 1.5 mm² Flexible Cable, 100 m Annealed Copper

RS Stock No: 606-115



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial applications. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable is suitable for installations requiring flexibility and a robust PVC jacket for protection.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	1.5 mm ²
Cable Length	100 m
Core Strands	30/0.25
Jacket Material	Polyvinyl Chloride
Number of Cores	3
Outside Diameter	9.4 mm

Operation Environment Specifications

Maximum Operating Temperature	90 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------