


# AC2950



## Passive power distributor

ProcessLine 4SB IP69K



Depending on the version some LEDs are inactive



Application		
Design		AS-i oder IO-Link Spannungsverteiler
Application		hygienic and wet areas in the food industry
Electrical data		
Protection class		III
Overcurrent detection		yes; (4400 mA ± 200 mA)
AS-i operation		
Operating voltage	[V]	18...31.6 DC; (AS-i)
Current consumption	[mA]	4000; (AS-i)
Additional voltage supply	[V]	15...30 DC; (AUX)
Max. current consumption from additional supply	[mA]	4000; (AUX)
IO-Link operation		
Operating voltage	[V]	20...30 DC; (US)
Current consumption	[mA]	4000; (US)
Additional voltage supply	[V]	20...30 DC; (UA)

# AC2950



## Passive power distributor

ProcessLine 4SB IP69K

Max. current consumption from additional supply [mA]	4000; (UA)
--	------------

### Operating conditions

Ambient temperature [°C]	-25...60
Storage temperature [°C]	-25...85
Max. relative air humidity [%]	90; (non condensing)
Max. height above sea level [m]	4000
Protection	IP 65; IP 66; IP 67; IP 69K; (operation with stainless steel protective caps: IP 69K)
Protection rating (NEMA 250)	6P
Pollution degree	2
Chemical media	ISO 16750-5 HLP, CC, DB, DC, DD, CA NEMA 250 5.13.1 AA

### Tests / approvals

EMC	EN 62026-2 IEC 61000-6-2
Shock resistance	DIN EN 60068-2-27
Vibration resistance	DIN EN 60068-2-64 DIN EN 60068-2-6
MTTF [years]	379

### Mechanical data

Weight [g]	284.8
Housing	rectangular
Dimensions [mm]	152 x 59.3 x 38.4
Materials	housing: PA grey; plugs and sockets: stainless steel (316L/1.4404)

### Displays / operating elements

Display	operation LED, green AS-i / AUX / US / UA fault LED, red
---------	---

### Electrical connection


Module connection	M12
-------------------	-----

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection - Power IN

Connector: M12; coding: A; Tightening torque: 0.6...0.8 Nm



### AS-i operation

1	AS-i +
2	AUX -
3	AS-i -
4	AUX +

# AC2950



## Passive power distributor


ProcessLine 4SB IP69K

### IO-Link operation

1	+ 24 V DC (US)
2	GND (UA)
3	GND (US)
4	+ 24 V DC (UA)

### Electrical connection - Power OUT

Connector: M12; coding: A; Tightening torque: 0.6...0.8 Nm



### AS-i operation 1...4

1	AS-i +
2	AUX -
3	AS-i -
4	AUX +
5	n.c.

### IO-Link operation 1...4

1	+ 24 V DC (US)
2	GND (UA)
3	GND (US)
4	+ 24 V DC (UA)
5	n.c.