

Productname : ECO Supercut
Ref.Nr.: BDS000293_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: BDS000293_20150407

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

ECO Supercut
Bulk

1.2. Relevant identified uses of the substance or mixture and uses advised against

Lubricants

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Laurinkatu 57 A 23 B, 08100 Lohja	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südtring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Not classified

Classification is based on test data.

Health: Not classified

Classification based on calculation method.



Productname : ECO Supercut
Ref.Nr.: BDS000293_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: BDS000293_20150407

Environment: Not classified
Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

None

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

No health or environmental hazardous components in concentrations exceeding the limits for classification.

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water for several minutes Seek medical attention if irritation persists
Contact with skin :	Wash with water and soap. Seek medical attention if irritation persists
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	If swallowed do not induce vomiting Seek medical advice

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Low toxicity expected under normal conditions of use
Ingestion :	Low toxicity expected under normal conditions of use
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed



Productname : ECO Supercut
Ref.Nr.: BDS000293_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: BDS000293_20150407

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Forms hazardous decomposition products
CO, CO₂

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing including eye/face protection.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well ventilated areas
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.



Productname :	ECO Supercut	Creationdate :	29.06.17 Version : 2.0
Ref.Nr.:	BDS000293_3_20170629 (EN)	Replaces:	BDS000293_20150407

7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated place
Keep out of reach of children.

7.3. Specific end use(s)

Lubricants

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

No information available

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. It is good practice to wear gloves and to provide adequate ventilation whenever using the product. In all cases handle and use the product in accordance with good industrial hygiene practices.
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
hands and skin :	If handled correctly skin exposure will be accidental. In such case the use of disposable gloves should be sufficient provided they are changed immediately after a splash or spill may occur. If intentional contact is expected reusable gloves should be used with a breakthrough time greater than the total duration of the product use.
Recommended gloves:	(neoprene)
eyes :	Wear safety eyewear according to EN 166.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Apperance : physical state :	Liquid.
colour :	Yellow.
odour :	Characteristic odor.
pH :	Not applicable.
Boiling point/range :	Not available.
Flash point :	330 °C (Open Cup)
Evaporation rate :	Not applicable.



Productname : ECO Supercut
Ref.Nr.: BDS000293_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: BDS000293_20150407

Explosion limits : upper limit : Not available.
lower limit : Not available.
Vapour pressure : Not available.
Relative density : 0.910 g/cm³ (@ 20°C).
Solubility in water : Insoluble in water
Auto-ignition : > 250 °C

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO₂

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity: based on available data the classification criteria are not met
skin corrosion/irritation: based on available data the classification criteria are not met
serious eye damage/irritation: based on available data the classification criteria are not met
respiratory or skin sensitisation: based on available data the classification criteria are not met
germ cell mutagenicity: based on available data the classification criteria are not met
carcinogenicity: based on available data the classification criteria are not met
toxicity for reproduction: based on available data the classification criteria are not met
STOT-single exposure: based on available data the classification criteria are not met



Productname :	ECO Supercut	Creationdate :	29.06.17 Version : 2.0
Ref.Nr.:	BDS000293_3_20170629 (EN)	Replaces:	BDS000293_20150407

STOT repeated exposure: based on available data the classification criteria are not met
aspiration hazard: based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation :	Low toxicity expected under normal conditions of use
Ingestion :	Low toxicity expected under normal conditions of use
Skin contact :	May cause irritation.
Eye contact :	May cause irritation.

Toxicological data :

No information available

SECTION 12: Ecological information**12.1. Toxicity**

Not classified

Ecotoxicological data:

No information available

12.2. Persistence and degradability

Readily biodegradable - OECD 301B

12.3. Bioaccumulative potential

Log Pow > 4
no bioaccumulation expected

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available

SECTION 13: Disposal considerations

Productname :	ECO Supercut	Creationdate :	29.06.17 Version : 2.0
Ref.Nr.:	BDS000293_3_20170629 (EN)	Replaces:	BDS000293_20150407

13.1. Waste treatment methods

Product :	This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.
Contaminated packaging :	Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information**14.1. UN number**

UN-number :	Not classified as hazardous for transport
-------------	---

14.2. UN proper shipping name

Proper shipping name:	Not applicable.
-----------------------	-----------------

14.3. Transport hazard class(es)

Class:	Not applicable.
ADR/RID - Classification code:	Not applicable.

14.4. Packing group

Packing group:	Not applicable.
----------------	-----------------

14.5. Environmental hazards

ADR/RID - Environmentally hazardous:	No
IMDG - Marine pollutant:	No
IATA/ICAO - Environmentally hazardous:	No

14.6. Special precautions for user

ADR/RID - Tunnelcode:	Not applicable.
IMDG - Ems:	Not applicable.
IATA/ICAO - PAX:	Not applicable.
IATA/ICAO - CAO	Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

Productname :	ECO Supercut	Creationdate :	29.06.17 Version : 2.0
Ref.Nr.:	BDS000293_3_20170629 (EN)	Replaces:	BDS000293_20150407

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Regulation (EC) No 1907/2006 (REACH)
Regulation (EC) No 1272/2008 (CLP)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

REVISIONS IN CHAPTRE :	8.2. Exposure controls
acronyms and synonyms:	TWA = time weight average
	STEL = short time exposure limit
	VOC = volatile organic compounds
	PBT = persistant bioaccumulative toxic
	vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.