



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 6

Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Centerline (Pitch): **3.81 mm [.15 in]**

Number of Rows: 1

Features

Product Type Features

Header Type	Fully Shrouded
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	6
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Black
Product Orientation	Right Angle



Contact Features

Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Copper Magnesium
Contact Current Rating (Max)	11 A

Termination Features

Termination Post & Tail Length	1.9 mm[.075 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	High Temperature Polyamide
Centerline (Pitch)	3.81 mm[.15 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1986722-6
STR PLUG SPRING TYPE LH 6P, 3.81 mm



TE Part # 1986375-6
Str Plug, 3.81mm, Green, LH, 6



TE Part # 284507-6
6 POS TERMI-BLOK PLUG STAC 3,8



TE Part # 1986720-6
STR PLUG SPRING TYPE RH 6P, 3.81 mm



TE Part # 1986374-6
Str Plug, 3.81mm, Green, RH, 6

Customers Also Bought



TE Part #1986720-8
STR PLUG SPRING TYPE RH 8P, 3.81 mm



TE Part #T4141012081-000
M12,REAR MOUNT,FEMALE,A,8P, SOLDER PCB



TE Part #T4152599L14-002
RPC-M12L-4MS-1.0-4FS-PVC 14AWG BK



TE Part #T4151399L14-002
RPC-M12L-4FS-1.0-PVC 14AWG BK



TE Part #1986722-6
STR PLUG SPRING TYPE LH 6P, 3.81 mm



TE Part #1986711-8
SCREWLESS, SW,8P,5.0 PCB



TE Part #464431-E
M8 FEMALE, A CODE, 3P, 16.25MM SMT



TE Part #T41513C9L14-005
RPC-M12L-4FS-5.0-PUR 16AWG BK SMT



TE Part #284517-8
8P TERMIBLOK HDR DIR POL



TE Part #T41513B9L25-002
RPC-M12L-5FS-1.0-PUR 14AWG GY

Documents

Product Drawings

6POS HDR 90 DEG,HT,3.81MM PITCH,TL 1.9MM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2342077-6_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2342077-6_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2342077-6_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

Agency Approvals

UL

English