




TE Internal #: 63381-1
Receptacle Terminal, 3.17 mm [.125 in] Pin Diameter, 22 – 18 AWG, .
3 – .8 mm² Wire, 642 – 1624 CMA, 16.13 mm [.635 in] Length, Open
Barrel
[View on TE.com >](#)

Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Crimp Wire Terminal Type: **Receptacle Terminal**
Mating Pin Diameter: **3.17 mm [.125 in]**
Wire Size: **642 – 1624 CMA**

Features

Product Type Features

Compatible With Discrete Wire Type	Solid, Stranded
------------------------------------	-----------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

Crimp Wire Terminal Type	Receptacle Terminal
Mating Pin Diameter	3.17 mm[.125 in]
Barrel Type	Open
Terminal Plating Material	Unplated
Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	642 – 1624 CMA
Barrel Inside Diameter	1.01 mm[.04 in]
Terminal Material Thickness	.35 mm[.014 in]
Overall Product Length	16.13 mm[.635 in]



Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 2837046-1
[OCEAN_2.0_Applicator-S-070F-RSM](#)



TE Part # 60440-1
[PIN 093 RECEPTACLE 22-18 AWG BR](#)



TE Part # 7-2837046-7
[OCEAN_2.0_SPARE_PART_KIT-070F](#)




TE Part # 62402-1
[PIN .106 REC 22-18 AWG \(OR\) 22AWG PTPBR](#)



TE Part # 2837046-2
[OCEAN_2.0_Applicator-S-070F-RSA](#)



TE Part # 160784-3
[REC.FOR 2,5 DIA PIN](#)



TE Part # 62505-1
[PIN 130 22-18 AWG .0157 X 1.020 BR](#)

Customers Also Bought



TE Part #T4141012041-000
[M12,REAR MOUNTING,FEMALE,A CODE,4P](#)



TE Part #T4113001041-000
[M12,MALE,RA,A CODE,4P,PG7,GOLD](#)



TE Part #413985-3
[PLUG ASSY,STR,SMB](#)



TE Part #414026-3
[JACK ASSY,SMB,RT ANG](#)



TE Part #440053-5
[2.5MM,HDR,5POS,R/A](#)




TE Part #1-1623925-5
[CFR100 5% 1K0](#)




TE Part #4-1825059-1
[ADF08ST04=DIP SWT,FLUSH,SMT-GW](#)



TE Part #1939115-1
[SD CONN STD EMBOSS W/B REVERSE](#)



TE Part #2311763-1
[AMPL REC, HD22, R/A, 15P, S/L](#)



TE Part #6-5530843-5
[CONN SEC II 31 POS 100C/L](#)

Documents



Product Drawings

PIN .125 TERMINAL REC 22-18 AWG BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63381-1_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_63381-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63381-1_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Pin Receptacle Contact With Closed Seam

English