



### Main

Range	Acti 9
Product name	Disbo iC60
Product or component type	Miniature circuit-breaker
Device short name	IC60N
Poles description	4P
Number of protected poles	4
[In] rated current	20 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	6 kA Icu conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 10 kA Icu conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 20 kA Icu conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 6 kA Icu conforming to EN/IEC 60947-2 - 100...133 V DC 36 kA Icu conforming to EN/IEC 60947-2 - 12...133 V AC 50/60 Hz 6000 A Icn conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz
Utilisation category	Category A conforming to EN/IEC 60947-2

### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	440 V AC 50/60 Hz
Magnetic tripping limit	8 x In +/- 20 %
[Ics] rated service breaking capacity	7.5 kA 75 % x Icu conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 15 kA 75 % x Icu conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 6 kA 100 % x Icu conforming to EN/IEC 60947-2 - 100...133 V DC 27 kA 75 % x Icu conforming to EN/IEC 60947-2 - 12...133 V AC 50/60 Hz 6000 A 100 % x Icu conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz 4.5 kA 75 % x Icu conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz
Limitation class	3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2

Contact position indicator	Yes
Control type	Toggle
Local signalling	Trip indicator
Mounting mode	Clip-on
Mounting support	Rail
9 mm pitches	8
Height	85 mm
Width	72 mm
Depth	78.5 mm
Product weight	0.5 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Single terminal, top or bottom rigid wire(s) 1...25 mm <sup>2</sup> max Single terminal, top or bottom flexible wire(s) 1...16 mm <sup>2</sup> max
Wire stripping length	14 mm top or bottom
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Separate block

## Environment

Standards	EN/IEC 60947-2 EN/IEC 60898-1
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % ( 55 °C )
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations