



ENGLISH

Datasheet

Stock No: 121-6859

RS Pro Motor Protection Switch

Specifications:

- Versions: - MS32 - with thermal and magnetic releases
- Manual control: - START, STOP, push-buttons - with a trip indication (i.e. push-buttons stay in the middle position)
- Automatic switch-off at over-current with thermal or magnetic release
- Control with under-voltage release or shunt release
- An auxiliary switch for side mounting or flush mounting used for indication of the switching state
- Indication of release with trip indicating auxiliary switch
- ON/OFF buttons position unequivocally indicates switching position of main circuit contacts
- Contact material - Resistant to contact welding - Enables low contact heating
- Isolating distance between contacts: 4.5 mm per contact place
- Connection of a rigid or flexible conductor
- Assembly to 35 mm wide mounting rail in compliance with EN 60715
- Vertical or horizontal operational position

Technical Specification

GENERAL	Standards			IEC/EN 60947-2, IEC/EN 60947-4-1, IEC/EN 60947-5-1, IEC/EN 60204, UL 508, CSA 22.2 No.14
	Approvals			UL
	Climatic class			constant damp heat acc. to IEC 60068-2-78 cyclic damp heat acc. to IEC 60068-2-30
	Degree of protection			IP20, after terminals covering IP40
	Ambient temperature		°C	-25 ... +60
	Storage temperature		°C	-25 ... +70
	Temperature range of thermal compensation for overload release		°C	-5 ... +40
	Mechanical and electrical endurance		op. c.	100,000
	Max. operating cycles		op. / h	25
	Shock resistance acc. to IEC 68-2-27		g	20
	Vibration resistance acc. to IEC 68-2-6			5 g at f = 5 ... 150 Hz
	Overvoltage category / pollution degree			III / 3
	Rated insulation voltage	U_i	V	690
	Rated impulse withstand voltage	U_{imp}	kV	6
Weight		kg	0.279	
MAIN CIRCUIT	Designation of connection terminals			1 - L1 ; 3 - L2 ; 5 - L3 ; 2 - T1 ; 4 - T2 ; 6 - T3
	Terminal capacity	rigid flexible	S	mm ² 0.75 ... 10 0.75 ... 6
	Screw			with self-lifting clamp, protected against drop out
	Screw head			PZ2
	Tightening torque		Nm	2.0

Technical Specification

MAIN CIRCUIT				MS32 / MS18	MSB32 / MSB18	
	Max. operational voltage	U_e	V	690	400	
	Setting range		A	0.1 - 0.16; 0.16 - 0.25; 0.25 - 0.4; 0.4 - 0.63; 0.63 - 1; 1 - 1.6; 1.6 - 2.5; 2.5 - 4; 4 - 6.3; 6.3 - 10; 9 - 14; 13 - 18; 17 - 23 (only MS32); 20 - 27 (only MS32); 25 - 32 (only MS32)	0.25 - 0.4; 0.4 - 0.63; 0.63 - 1; 1 - 1.6; 1.6 - 2.5; 2.5 - 4; 4 - 6.3; 6.3 - 10; 9 - 14; 13 - 18; 17 - 23 (only MSB32); 20 - 27 (only MSB32); 25 - 32 (only MSB32)	
	No. of poles			3		
	Operating current of thermal overload release		I	$1,05 I_r < I \leq 1,20 I_r$ I_r ...current setting value		
	Sensitivity to phase failure			yes		
	Power dissipation per pole at the upper setting limit		P	W	2 - 2,5	
	Utilization category acc. to IEC/EN 60947-4-1				AC-3	
	acc. to IEC/EN 60947-2				A	
	Trip class acc. To IEC/EN 60947-4-1				10	

Technical Specification

Standard motor powers						Setting range
Single-phase	Three-phase					
220 V 230 V 240 V	220 V 230 V 240 V	380 V 400 V 415 V	440 V	500 V	660 V 690 V	
kW						A
					0.06	0.1 ... 0.16
		0.06	0.06	0.06 ... 0.9	0.06 ... 0.12	0.16 ... 0.25
	0.06	0.09	0.12	0.09 ... 0.12	0.18	0.25 ... 0.4
	0.09	0.12 ... 0.18	0.18	0.18	0.25	0.4 ... 0.63
0.06 ... 0.09	0.09 ... 0.12	0.18 ... 0.25	0.25 ... 0.37	0.25 ... 0.37	0.37 ... 0.55	0.63 ... 1
0.12	0.18 ... 0.25	0.37 ... 0.55	0.37 ... 0.55	0.55 ... 0.75	0.75 ... 1.1	1 ... 1.6
0.18 ... 0.25	0.37	0.75	0.75 ... 1.1	1.1	1.5	1.6 ... 2.5
0.37	0.55 ... 0.75	1.1 ... 1.5	1.5	1.5 ... 2.2	2.2 ... 3	2.5 ... 4
0.55 ... 0.75	1.1 ... 1.5	2.2	2.2 ... 3	2.2 ... 3	4	4 ... 6.3
1.1 ... 1.5	1.5 ... 2.2	3 ... 4	4	4 ... 5.5	5.5 ... 7.5	6.3 ... 10
2.2	2.2 ... 3	5.5	5.5 ... 7.5	5.5 ... 7.5	9 ... 11	9 ... 14
3	4	7.5	7.5 ... 9	9 ... 11	15	13 ... 18
	5.5	9 ... 11	11	11	15 ... 18.5	17 ... 23
	5.5 ... 7.5	11	11	15	18.5 ... 22	20 ... 27
	7.5	15	15	18.5	22	25 ... 32

Technical Specification

Type		Operating current of short-circuit release (A)	Rated ultimate short-circuit breaking capacity $I_{cu} \cdot I_{cs}$ (kA)								Max. back-up fuse, if $I_{cp} > I_{cu}$ (gL) (A)					
			230 V		400 V		500 V		690 V		230 V	400 V	500 V	690 V		
			I_{cu}	I_{cs}	I_{cu}	I_{cs}	I_{cu}	I_{cs}	I_{cu}	I_{cs}						
MS32 - 0.16	MS18 - 0.16	2	100	100	100	100	100	100	100	100	No back-up fuse required					
MS32 - 0.25	MS18 - 0.25	3	100	100	100	100	100	100	100	100						
MS32 - 0.4	MS18 - 0.4	5	100	100	100	100	100	100	100	100						
MS32 - 0.63	MS18 - 0.63	8	100	100	100	100	100	100	100	100						
MS32 - 1	MS18 - 1	13	100	100	100	100	100	100	100	100						
MS32 - 1.6	MS18 - 1.6	22	100	100	100	100	100	100	100	100						
MS32 - 2.5	MS18 - 2.5	33	100	100	100	100	100	100	5	5					16	
MS32 - 4	MS18 - 4	55	100	100	100	100	100	100	3	3					25	
MS32 - 6.3	MS18 - 6.3	84	100	100	100	100	6	4.5	3	2					35	35
MS32 - 10	MS18 - 10	126	100	100	100	100	6	4.5	3	2					50	35
MS32 - 14	MS18 - 14	170	25	12.5	25	12.5	6	4.5	3	2	80	63	50	50		
MS32 - 18	MS18 - 18	230	25	12.5	25	12.5	6	4.5	3	2	80	63	50	50		
MS32 - 23		270	25	12.5	25	12.5	4	3	3	2	80	80	50	50		
MS32 - 27		360	25	12.5	25	12.5	4	3	3	2	80	80	50	50		
MS32 - 32		400	25	12.5	25	12.5	4	3	3	2	80	80	50	50		

HS - Auxiliary Switch



HS - Auxiliary switch

HS 11 - with 1 make and 1 break contact
 HS 10 - with 1 make contact
 HS 20 - with 2 make contacts

Rated insulation voltage	U_i	V	500
Thermal current	I_{th}	A	5
Electrical rating acc. to IEC/EN 60947-5-1			
B300	AC-15	U_e	V 240
		I_e	A 1,5
R300	DC-13	U_e	V 250
		I_e	A 0,1
Terminal capacity	S	mm ²	0,75 ... 2,5
Tightening torque		Nm	1

HSV - Auxiliary Contact Block

HRS – Trip Indicating Contact Block



HSV - Auxiliary contact block* HRS - Trip indicating contact block**

HSV 10 - with 1 make contact
 HSV 01 - with 1 break contact
 HRS 10 - with 1 make contact
 HRS 01 - with 1 break contact

Rated insulation voltage	U_i	V	300
Thermal current	I_{th}	A	1
Electrical rating acc. to IEC/EN 60947-5-1			
B300	AC-15	U_e	V 240
		I_e	A 1,5
R300	DC-13	U_e	V 125
		I_e	A 0,22
Terminal capacity	S	mm ²	0,75 ... 2,5
Tightening torque		Nm	1

UR - Under Voltage Release

AR – Shunt Releases



UR - Under-voltage release AR - Shunt release

Control voltages	U_c	V	24 ... 600
Rated frequency	f	Hz	50 or 60
Terminal capacity	S	mm ²	0,75 ... 2,5
Tightening torque		Nm	1

MSK – Connection Blocks

MSK07, MSKNL6-22 adapters are used for connecting a motor protection switch with a contactor forming a single-unit starter for quick assembly to a 35 mm wide mounting rail (EN 60715).



Accessories



HO-41 and 55 Enclosure



Padlock Feature



Emergency Stop Push-Button