


## **DVR 2 BY S 150 FM (928 430)**

- For electroacoustic systems up to 10 A
- Direct plug-in technology allows connection without tools
- For installation in conformity with the lightning protection zone concept at the boundaries 0<sub>A</sub> 2 and higher








Figure without obligation

Basic circuit diagram DVR 2 BY S 150 FM

Dimension drawing DVR 2 BY S 150 FM

Compact combined arrester for protecting electroacoustic systems (e.g. voice alarm systems, loudspeaker systems). Protection of one galvanically isolated pair; direct or indirect shield earthing. Direct plug-in technology allows fast conductor connection without tools. Easy replacement of the arrester is ensured by the integrated terminal units which can be released and then removed from the enclosure. Integrated remote signalling contact (break contact).

## **Technical data**

Туре	DVR 2 BY S 150 FM
Part No.	928 430
SPD class	TYPE 1/P2
Nominal voltage (a.c.) (U <sub>N</sub> )	100 V
Max. continuous operating voltage (d.c.) (U <sub>c</sub> )	150 V
Max. continuous operating voltage (a.c.) (U <sub>c</sub> )	110 V
Nominal current at 70 °C (I <sub>L</sub> )	10 A
Nominal current at 80 °C (I <sub>L</sub> )	7 A
D1 Lightning impulse current (10/350 μs) per line (I <sub>imp</sub> )	2.5 kA
D1 Total lightning impulse current (10/350 µs) (I <sub>imp</sub> )	9 kA
C2 Nominal discharge current (8/20 µs) per line (In)	7.5 kA
C2 Total nominal discharge current (8/20 µs) (In)	22.5 kA
Voltage protection level line-line at I <sub>imp</sub> D1 (U <sub>p</sub> )	≤ 500 V
Voltage protection level line-PG at I <sub>imp</sub> D1 (U <sub>p</sub> )	≤ 700 V
Voltage protection level line-line at 1 kV/µs C3 (Up)	≤ 400 V
Voltage protection level line-PG at 1 kV/µs C3 (U <sub>P</sub> )	≤ 650 V
Cut-off frequency line-line (f <sub>G</sub> )	1.4 MHz
Operating temperature range (T <sub>u</sub> )	-40 °C +80 °C
Degree of protection	IP 20
Capacity	2 module(s), DIN 43880
For mounting on	35 mm DIN rails acc. to EN 60715
Connection (input / output)	spring / spring
Cross-sectional area, solid	0.2-1.5 mm <sup>2</sup>
Cross-sectional area, flexible	0.2-1.5 mm <sup>2</sup>
Earthing via	DIN rail
Enclosure material	thermoplastic, UL 94 V-0
Colour	yellow
Test standards	IEC 61643-21 / EN 61643-21
Approvals	EAC
Type of remote signalling contact	break contact
Switching capacity (d.c.)	250 V / 0.1 A; 125 V / 0.2 A; 75 V / 0.5 A
Switching capacity (a.c.)	250 V / 0.5 A
Cross-sectional area for remote signalling terminals	max. 1.5 mm <sup>2</sup>
Weight	110 g
Customs tariff number (Comb. Nomenclature EU)	85363010
GTIN	4013364261389
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.