

## FEATURES

- Silver plated copper conductor
- PTFE Insulation to BS3G 210
- Various wire sizes and strands
- Multiple colours, including orange, blue, white and red

# RS PRO PTFE Equipment Wire 0.22 mm<sup>2</sup> CSA, Black 100m Reel

RS Stock No.: 841-7223



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Brought to you by RS PRO, a range of wire and cables which excel within harsh environments. In areas where contamination causes an issue, such as oils, acids or excessive sunlight, these cables are specifically designed to be used within those areas. Highlighted by their copper conductor, these cables are suitable for various applications. All models are highly reliable and excellent quality.

## General Specifications

<b>Type</b>	A
<b>Wire Style</b>	BS3G210
<b>American Wire Gauge</b>	24
<b>Insulation Material</b>	PTFE
<b>Resistant To</b>	Fuels, Gasoline, Hydraulic Fluid, Lubricants, Oils
<b>Core Strands</b>	7/0.2mm
<b>Conductor Material</b>	Silver Plated Copper
<b>Number of Strands</b>	7
<b>Applications</b>	Construction sites, Car engines, Aeroplanes, Petrol stations

## Electrical Specifications

<b>Voltage Rating</b>	300V
<b>Current Rating</b>	6A
<b>Conductor resistance</b>	88.3Ω /km

## Mechanical Specifications

<b>Cross Sectional Area</b>	0.22mm <sup>2</sup>
<b>Sheath Colour</b>	Black
<b>Length</b>	100m
<b>Outer Diameter</b>	0.95mm
<b>Insulation Wall Thickness</b>	0.15mm
<b>Size of Strands</b>	0.2mm
<b>Stranding</b>	7/0.2mm
<b>weight</b>	3.04kg/km

## Operation Environment Specifications

<b>Minimum Operating Temperature</b>	-75°C
<b>Maximum Operating Temperature</b>	200°C
<b>Operating Temperature Range</b>	-75°C to 200°C

## Approvals

<b>Compliance/Certifications</b>	CSA , RoHS Certificate Of Compliance
<b>Standards Met</b>	BS 3G 210:1996





- 8417213 8417223
- 8417241
- 8417245
- 8417226 8417235
- 8417257
- 8417251
- 8417217 8417232
- 8417260
- 8417254
- 8417248
- 8417239

**Product Range:**

<b>RS Code</b>	<b>Description</b>
8417213	PTFE A 7/0.2 black 25m
8417229	PTFE A 7/0.2 white 25m
8417217	PTFE A 7/0.2 pink 25m
8417226	PTFE A 7/0.2 red 25m
8417232	PTFE A 7/0.2 pink 100m
8417235	PTFE A 7/0.2 red 100m
8417223	PTFE A 7/0.2 black 100m
8417241	PTFE A 7/0.2 blue 100m
8417239	PTFE A 7/0.2 white 100m
8417248	PTFE A 7/0.2 yellow 100m
8417245	PTFE A 7/0.2 orange 100m
8417254	PTFE A 7/0.2 green 100m
8417257	PTFE A 7/0.2 brown 100m
8417260	PTFE A 7/0.2 grey 100m
8417251	PTFE A 7/0.2 violet 100m

