Specifications
μ [mju:]-II ZOOM 80

Type:	Full-automatic 35 mm autofocus lens-shutter camera with built-in 38 ~ 80 mm zoom lens.
Film format:	35 mm standard DX-coded film (24 x 36 mm).
Lens:	Olympus lens 38 ~ 80 mm, F4.5 ~ 8.9 (5 elements in 4 groups).
Shutter:	Programmed electronic shutter.
Viewfinder:	Real image zoom viewfinder (with autofocus mark, close-up correction marks, autofocus indicator and flash indicator).
Focusing:	Active-type multi-beam autofocus system. Focus lock possible. Focusing Range: 0.6 m ~ ∞ (infinity). Fixed at ∞ (infinity) in infinity mode.
Exposure control:	Programmed automatic exposure control, 2-zone light metering. Auto Exposure Range: Wide: EV 2.4 ~ EV 16 Tele: EV 4.3 ~ EV 17
Exposure compensation:	+1.5 EV.
Exposure counter:	Progressive type with automatic reset, displayed on LCD panel.
Self-timer:	Electronic self-timer with approx. 12 sec. delay.
Remote control (optional):	Infrared remote control unit with approx. 3 sec. delay.
Film speed range:	Automatic setting with DX-coded film with ISO 50, 100, 200, 400, 800, 1600 and 3200. Film speeds other than those above will be automatically set to the next lower speed. For non DX-coded film and film with less than ISO 50, film speed is set to ISO 100.
Film loading:	Automatic loading. (Automatically advances to first frame when camera back cover is closed.).
Film advance:	Automatic film winding.
Film rewind:	Automatic film rewind (automatic rewind activation at end of film, automatic rewind stop). Rewind possible at any point with rewind button.
Flash:	Built-in flash.
Recycling time:	Approx. 0.5 ~ 7 sec. (at normal temperature with new battery).
Flash working range:	With ISO 100 colour negative film: Wide: 0.6 ~ 4.4 m Tele: 0.6 ~ 2.2 m With ISO 400 colour negative film: Wide: 0.6 ~ 8.8 m Tele: 0.6 ~ 4.4 m
Flash modes:	Auto, Red-Eye Reducing Flash, Off, Fill-In Flash, Night Scene Flash and Red-Eye Reducing Night Scene Flash.
Battery check:	Displayed on LCD panel.
Weatherproof:	IEC Standard publication 529. Classification of degrees of protection provided by enclosures. Degree of protection indicated by the second characteristics numeral 4. • Short description: Protected against splashing water. • Definition: Water splashed against the enclosure from any direction shall have no harmful effect. • Test for second numeral 4: The equipment is sprayed from all directions.
Power source:	One 3 V lithium battery (DL 123A / CR 123A).
Dimensions:	115 (W) x 59.5 (H) x 39.5 (D) mm

	(without grip and other protrusions).
Weight:	185 g (without battery).

Date Unit Specifications (Quartzdate model only)

Imprinting direction:	Data imprinted onto film from lens side.
Data coding:	No data, year-month-day, month-day-year, day-month-year and day-hour-minute.
External indication of data:	Data display on LCD panel.
Film speed setting:	Automatic film speed setting.
Automatic calendar system:	Up to year 2030.
Power source:	Ordinarily used with camera body.